

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205378

Luminaire Tested: **LE\_6B10D010 EC6B10209727 6LBSLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205378  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B10D010 EC6B10209727 6LBSLI1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1022.9 lumens  
Efficiency: N/A  
Efficacy: 103.3 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205378

CATALOG NUMBER: LE\_6B10D010 EC6B10209727 6LBSLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P205378

CATALOG NUMBER: LE\_6B10D010 EC6B10209727 6LBSLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205378

CATALOG NUMBER: LE\_6B10D010 EC6B10209727 6LBSLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	59.5	5.8
10°-20°	151.4	14.8
20°-30°	193.1	18.9
30°-40°	200.3	19.6
40°-50°	184.5	18.0
50°-60°	138.8	13.6
60°-70°	74.9	7.3
70°-80°	20.1	2.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	404.0	39.5
0°-40°	604.3	59.1
0°-60°	927.6	90.7
0°-90°	1022.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1022.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	646	
5°	636	59
15°	540	151
25°	420	193
35°	320	200
45°	240	184
55°	155	139
65°	75	75
75°	17	20
85°	0	0
90°	0	



TEST NUMBER: P205378

CATALOG NUMBER: LE\_6B10D010 EC6B10209727 6LBSLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	645.5
2.5°	643.4
5°	635.8
7.5°	621.6
10°	596.6
12.5°	571.6
15°	540.1
17.5°	510.8
20°	480.4
22.5°	448.9
25°	419.5
27.5°	391.2
30°	365.1
32.5°	341.2
35°	319.5
37.5°	298.9
40°	279.2
42.5°	258.6
45°	240.1
47.5°	219.5
50°	198.9
52.5°	177.1
55°	155.4
57.5°	133.6
60°	113.0
62.5°	93.5
65°	75.0
67.5°	57.6
70°	42.4
72.5°	29.4
75°	17.4
77.5°	7.6
80°	2.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)