

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P252809

Luminaire Tested: **LE\_6B40D010 EC6B30509024 6LBBA1MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P252809  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-2)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B40D010 EC6B30509024 6LBBA1MW  
Description: PORTFOLIO 6 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4801.3 lumens  
Efficiency: N/A  
Efficacy: 111.7 lumens/watt  
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1  
Luminous Opening: Circular (Dia: 0.46' x H: 0')  
CIE Type: Direct


Input Watts (W): 43  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P252809

CATALOG NUMBER: LE\_6B40D010 EC6B30509024 6LBBA1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P252809

CATALOG NUMBER: LE\_6B40D010 EC6B30509024 6LBBA1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88				88
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78				78
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69				69
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62				62
5	84	73	65	60	82	72	65	60	70	64	59	68	63	58	66	62	58	56				56
6	78	67	60	54	77	66	59	54	65	58	54	63	57	53	62	57	53	51				51
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	47				47
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	53	48	44	43				43
9	65	54	46	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39				39
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37				37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	214844
5°	212868
10°	208181
15°	201573
20°	193432
25°	181582
30°	157130
35°	122341
40°	92992
45°	72483
50°	60126
55°	53960
60°	49126
65°	45324
70°	41660
75°	38592
80°	34903
85°	31888



TEST NUMBER: P252809

CATALOG NUMBER: LE\_6B40D010 EC6B30509024 6LBBA1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	306.8	6.4
10°-20°	838.5	17.5
20°-30°	1142.0	23.8
30°-40°	966.4	20.1
40°-50°	619.9	12.9
50°-60°	426.6	8.9
60°-70°	291.4	6.1
70°-80°	162.2	3.4
80°-90°	47.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2287.3	47.6
0°-40°	3253.7	67.8
0°-60°	4300.2	89.6
0°-90°	4801.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4801.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3293	
5°	3250	307
15°	2984	839
25°	2522	1142
35°	1536	966
45°	786	620
55°	474	427
65°	294	291
75°	153	162
85°	43	47
90°	0	



TEST NUMBER: P252809

CATALOG NUMBER: LE\_6B40D010 EC6B30509024 6LBBA1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3293.1
2.5°	3280.5
5°	3250.4
7.5°	3202.8
10°	3142.5
12.5°	3067.2
15°	2984.4
17.5°	2889.0
20°	2786.1
22.5°	2670.6
25°	2522.5
27.5°	2321.8
30°	2085.8
32.5°	1814.8
35°	1536.1
37.5°	1292.6
40°	1091.9
42.5°	923.6
45°	785.6
47.5°	677.8
50°	592.4
52.5°	527.1
55°	474.4
57.5°	424.1
60°	376.5
62.5°	333.9
65°	293.6
67.5°	253.5
70°	218.4
72.5°	183.2
75°	153.1
77.5°	123.0
80°	92.9
82.5°	67.8
85°	42.6
87.5°	17.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)