

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204964

Luminaire Tested: **LE_6B10D010 EC6B10208030 6LBCS1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204964
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10208030 6LBCS1MMS
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1366.6 lumens
Efficiency: N/A
Efficacy: 138.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204964

CATALOG NUMBER: LE_6B10D010 EC6B10208030 6LBCS1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P204964

CATALOG NUMBER: LE_6B10D010 EC6B10208030 6LBCS1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	83	80	78	76			76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65			65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50			50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44			44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40			40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36			36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32			32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29			29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204964

CATALOG NUMBER: LE_6B10D010 EC6B10208030 6LBCS1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.1	4.3
10°-20°	166.0	12.1
20°-30°	242.4	17.7
30°-40°	277.3	20.3
40°-50°	266.4	19.5
50°-60°	205.8	15.1
60°-70°	114.8	8.4
70°-80°	33.4	2.4
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	467.5	34.2
0°-40°	744.7	54.5
0°-60°	1217.0	89.1
0°-90°	1366.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1366.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	628	
5°	622	59
15°	589	166
25°	527	242
35°	444	277
45°	347	266
55°	231	206
65°	115	115
75°	29	33
85°	1	1
90°	0	



TEST NUMBER: P204964

CATALOG NUMBER: LE_6B10D010 EC6B10208030 6LBCS1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	627.6
2.5°	627.6
5°	622.2
7.5°	619.6
10°	610.8
12.5°	600.1
15°	588.8
17.5°	577.2
20°	560.4
22.5°	547.1
25°	526.9
27.5°	506.5
30°	486.1
32.5°	465.9
35°	443.8
37.5°	421.6
40°	396.0
42.5°	373.0
45°	347.4
47.5°	318.2
50°	290.8
52.5°	260.8
55°	230.8
57.5°	199.8
60°	170.6
62.5°	141.4
65°	114.9
67.5°	90.1
70°	67.1
72.5°	46.9
75°	29.1
77.5°	15.0
80°	5.2
82.5°	1.8
85°	0.9
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)