

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202854

Luminaire Tested: **LE\_6B40D010 EC6B30509024 6LBWWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202854  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B40D010 EC6B30509024 6LBWWH1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57  
W DL3-44.71 W DLE-39.33 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3450.0 lumens  
Efficiency: N/A  
Efficacy: 82.5 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202854

CATALOG NUMBER: LE\_6B40D010 EC6B30509024 6LBWWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P202854

CATALOG NUMBER: LE\_6B40D010 EC6B30509024 6LBWWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	71	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202854

CATALOG NUMBER: LE\_6B40D010 EC6B30509024 6LBWWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	206.0	6.0
10°-20°	612.5	17.8
20°-30°	922.0	26.7
30°-40°	942.7	27.3
40°-50°	572.5	16.6
50°-60°	161.2	4.7
60°-70°	24.5	0.7
70°-80°	8.0	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1740.5	50.4
0°-40°	2683.2	77.8
0°-60°	3416.9	99.0
0°-90°	3450.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3450.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2143	
5°	2152	206
15°	2169	612
25°	2013	922
35°	1528	943
45°	736	573
55°	160	161
65°	22	24
75°	9	8
85°	0	1
90°	0	



TEST NUMBER: P202854

CATALOG NUMBER: LE\_6B40D010 EC6B30509024 6LBWWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2142.9
2.5°	2142.9
5°	2151.5
7.5°	2164.5
10°	2164.5
12.5°	2173.1
15°	2168.8
17.5°	2160.1
20°	2129.9
22.5°	2086.5
25°	2013.0
27.5°	1930.8
30°	1818.1
32.5°	1684.0
35°	1528.1
37.5°	1355.0
40°	1155.9
42.5°	948.0
45°	735.9
47.5°	545.5
50°	385.2
52.5°	259.8
55°	160.1
57.5°	95.2
60°	47.6
62.5°	30.2
65°	21.6
67.5°	17.4
70°	13.0
72.5°	8.6
75°	8.6
77.5°	4.4
80°	4.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)