

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204861

Luminaire Tested: **LE_6B10D010 EC6B10208030 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204861
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10208030 6LBCSMB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1233.1 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204861

CATALOG NUMBER: LE_6B10D010 EC6B10208030 6LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P204861

CATALOG NUMBER: LE_6B10D010 EC6B10208030 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88			88
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			75
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65			65
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56			56
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49			49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43			43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39			39
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35			35
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31			31
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28			28

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204861

CATALOG NUMBER: LE_6B10D010 EC6B10208030 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.3	4.0
10°-20°	140.3	11.4
20°-30°	210.9	17.1
30°-40°	250.3	20.3
40°-50°	247.6	20.1
50°-60°	194.5	15.8
60°-70°	109.1	8.8
70°-80°	30.6	2.5
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	400.5	32.5
0°-40°	650.8	52.8
0°-60°	1092.9	88.6
0°-90°	1233.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1233.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	521	
5°	520	49
15°	498	140
25°	458	211
35°	401	250
45°	323	248
55°	219	195
65°	109	109
75°	26	31
85°	0	0
90°	0	



TEST NUMBER: P204861

CATALOG NUMBER: LE_6B10D010 EC6B10208030 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	520.8
2.5°	518.9
5°	519.9
7.5°	515.4
10°	510.1
12.5°	503.9
15°	497.8
17.5°	489.8
20°	479.1
22.5°	468.5
25°	457.9
27.5°	446.5
30°	431.4
32.5°	416.4
35°	401.4
37.5°	383.6
40°	363.4
42.5°	343.9
45°	322.6
47.5°	298.8
50°	274.0
52.5°	245.8
55°	219.2
57.5°	189.1
60°	160.9
62.5°	135.2
65°	108.8
67.5°	85.8
70°	63.6
72.5°	43.4
75°	26.5
77.5°	13.2
80°	3.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)