

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203520

Luminaire Tested: **LE_6B10D010 EC6B10208030 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203520
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10208030 6LBMMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1065.5 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203520

CATALOG NUMBER: LE_6B10D010 EC6B10208030 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203520

CATALOG NUMBER: LE_6B10D010 EC6B10208030 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89				89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79				79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71				71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64				64
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58				58
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53				53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48				48
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44				44
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41				41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38				38

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203520

CATALOG NUMBER: LE_6B10D010 EC6B10208030 6LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.5	6.9
10°-20°	196.7	18.5
20°-30°	264.2	24.8
30°-40°	216.7	20.3
40°-50°	130.1	12.2
50°-60°	86.4	8.1
60°-70°	58.0	5.4
70°-80°	31.2	2.9
80°-90°	8.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	534.4	50.1
0°-40°	751.0	70.5
0°-60°	967.6	90.8
0°-90°	1065.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1065.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	795	
5°	782	73
15°	701	197
25°	582	264
35°	344	217
45°	165	130
55°	96	86
65°	59	58
75°	29	31
85°	7	9
90°	0	



TEST NUMBER: P203520

CATALOG NUMBER: LE_6B10D010 EC6B10208030 6LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	795.1
2.5°	789.2
5°	781.9
7.5°	765.8
10°	746.6
12.5°	723.1
15°	701.1
17.5°	674.6
20°	648.1
22.5°	618.8
25°	582.0
27.5°	537.9
30°	479.1
32.5°	413.0
35°	343.9
37.5°	285.1
40°	235.1
42.5°	195.5
45°	164.6
47.5°	139.6
50°	122.0
52.5°	107.2
55°	95.5
57.5°	85.2
60°	76.4
62.5°	66.1
65°	58.8
67.5°	50.0
70°	42.6
72.5°	35.2
75°	29.4
77.5°	23.5
80°	17.6
82.5°	13.2
85°	7.4
87.5°	3.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)