

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204035

Luminaire Tested: **LE_6B10D010 EC6B10208030 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204035
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10208030 6LBNMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 959.1 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204035

CATALOG NUMBER: LE_6B10D010 EC6B10208030 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204035

CATALOG NUMBER: LE_6B10D010 EC6B10208030 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66			
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204035

CATALOG NUMBER: LE_6B10D010 EC6B10208030 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.0	7.6
10°-20°	193.6	20.2
20°-30°	258.5	26.9
30°-40°	208.5	21.7
40°-50°	99.9	10.4
50°-60°	59.2	6.2
60°-70°	39.4	4.1
70°-80°	21.1	2.2
80°-90°	5.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	525.1	54.8
0°-40°	733.6	76.5
0°-60°	892.7	93.1
0°-90°	959.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	959.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	786	
5°	777	73
15°	689	194
25°	566	258
35°	334	209
45°	124	100
55°	66	59
65°	40	39
75°	20	21
85°	5	6
90°	0	



TEST NUMBER: P204035

CATALOG NUMBER: LE_6B10D010 EC6B10208030 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	786.5
2.5°	786.5
5°	777.4
7.5°	762.1
10°	740.8
12.5°	718.0
15°	689.0
17.5°	661.5
20°	631.0
22.5°	599.0
25°	565.5
27.5°	530.5
30°	480.1
32.5°	410.0
35°	333.9
37.5°	263.8
40°	204.2
42.5°	158.5
45°	123.5
47.5°	97.5
50°	82.2
52.5°	73.1
55°	65.5
57.5°	59.5
60°	51.9
62.5°	45.8
65°	39.6
67.5°	33.5
70°	29.0
72.5°	24.4
75°	19.9
77.5°	15.2
80°	12.2
82.5°	9.1
85°	4.6
87.5°	1.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)