

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203319

Luminaire Tested: **LE\_6B10D010 EC6B10209030 6LBMWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203319  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B10D010 EC6B10209030 6LBMWH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 895.8 lumens  
Efficiency: N/A  
Efficacy: 90.5 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203319

CATALOG NUMBER: LE\_6B10D010 EC6B10209030 6LBMWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P203319

CATALOG NUMBER: LE\_6B10D010 EC6B10209030 6LBMWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87		
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81		
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76		
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71		
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66		
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62		
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58		
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55		
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203319

CATALOG NUMBER: LE\_6B10D010 EC6B10209030 6LBMWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.2	11.4
10°-20°	250.8	28.0
20°-30°	290.2	32.4
30°-40°	185.5	20.7
40°-50°	52.6	5.9
50°-60°	9.4	1.1
60°-70°	3.9	0.4
70°-80°	1.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	643.2	71.8
0°-40°	828.7	92.5
0°-60°	890.6	99.4
0°-90°	895.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	895.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1118	
5°	1098	102
15°	900	251
25°	640	290
35°	293	186
45°	61	53
55°	9	9
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P203319

CATALOG NUMBER: LE\_6B10D010 EC6B10209030 6LBMWH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1117.5
2.5°	1116.2
5°	1097.6
7.5°	1064.0
10°	1016.6
12.5°	961.8
15°	899.5
17.5°	834.8
20°	771.1
22.5°	708.9
25°	640.4
27.5°	565.6
30°	482.1
32.5°	388.8
35°	292.8
37.5°	211.8
40°	147.0
42.5°	97.1
45°	61.0
47.5°	36.1
50°	21.1
52.5°	12.5
55°	8.8
57.5°	7.5
60°	6.2
62.5°	5.0
65°	3.8
67.5°	2.5
70°	2.5
72.5°	1.2
75°	1.2
77.5°	1.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)