

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202952

Luminaire Tested: **LE_6B40D010 EC6B30508027 6LBWGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202952
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B40D010 EC6B30508027 6LBWGPH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3325.3 lumens
Efficiency: N/A
Efficacy: 79.6 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.11
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202952

CATALOG NUMBER: LE_6B40D010 EC6B30508027 6LBWGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P202952

CATALOG NUMBER: LE_6B40D010 EC6B30508027 6LBWGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82			
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74			
4	93	84	77	72	91	82	76	72	80	75	71	78	74	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	81	71	64	59	80	70	63	58	68	62	58	67	62	58	65	61	57	56			
7	76	65	58	53	75	65	58	53	63	57	53	62	57	53	61	56	52	51			
8	72	61	54	49	70	60	53	49	59	53	49	58	52	48	57	52	48	47			
9	68	57	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43			
10	64	53	46	42	63	52	46	42	51	45	41	51	45	41	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202952

CATALOG NUMBER: LE_6B40D010 EC6B30508027 6LBWGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	212.9	6.4
10°-20°	597.0	18.0
20°-30°	854.2	25.7
30°-40°	851.4	25.6
40°-50°	542.3	16.3
50°-60°	200.0	6.0
60°-70°	50.0	1.5
70°-80°	15.1	0.5
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1664.1	50.0
0°-40°	2515.5	75.6
0°-60°	3257.8	98.0
0°-90°	3325.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3325.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2260	
5°	2248	213
15°	2123	597
25°	1865	854
35°	1385	851
45°	698	542
55°	212	200
65°	46	50
75°	12	15
85°	0	2
90°	0	



TEST NUMBER: P202952

CATALOG NUMBER: LE_6B40D010 EC6B30508027 6LBWGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2260.0
2.5°	2260.0
5°	2248.5
7.5°	2225.6
10°	2197.0
12.5°	2162.8
15°	2122.6
17.5°	2071.1
20°	2014.0
22.5°	1951.0
25°	1865.2
27.5°	1773.6
30°	1653.5
32.5°	1527.6
35°	1384.6
37.5°	1213.0
40°	1035.6
42.5°	864.0
45°	698.0
47.5°	549.2
50°	412.0
52.5°	303.2
55°	211.8
57.5°	137.4
60°	91.5
62.5°	62.9
65°	45.8
67.5°	34.4
70°	28.6
72.5°	17.1
75°	11.5
77.5°	11.5
80°	5.8
82.5°	5.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)