

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202746

Luminaire Tested: **LE_6B40D010 EC6B30508027 6LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202746
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B40D010 EC6B30508027 6LBWH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4418.3 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202746

CATALOG NUMBER: LE_6B40D010 EC6B30508027 6LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202746

CATALOG NUMBER: LE_6B40D010 EC6B30508027 6LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202746

CATALOG NUMBER: LE_6B40D010 EC6B30508027 6LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	257.4	5.8
10°-20°	730.4	16.5
20°-30°	1070.8	24.2
30°-40°	1114.5	25.2
40°-50°	771.0	17.5
50°-60°	335.6	7.6
60°-70°	102.9	2.3
70°-80°	30.9	0.7
80°-90°	4.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2058.6	46.6
0°-40°	3173.1	71.8
0°-60°	4279.8	96.9
0°-90°	4418.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4418.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2725	
5°	2714	257
15°	2594	730
25°	2342	1071
35°	1803	1114
45°	996	771
55°	361	336
65°	97	103
75°	29	31
85°	6	5
90°	0	



TEST NUMBER: P202746

CATALOG NUMBER: LE_6B40D010 EC6B30508027 6LBWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2725.1
2.5°	2730.9
5°	2713.8
7.5°	2690.9
10°	2662.2
12.5°	2633.6
15°	2593.5
17.5°	2542.0
20°	2484.8
22.5°	2421.8
25°	2341.6
27.5°	2238.5
30°	2106.9
32.5°	1969.5
35°	1803.4
37.5°	1620.2
40°	1408.4
42.5°	1196.5
45°	996.1
47.5°	807.2
50°	641.2
52.5°	486.6
55°	360.6
57.5°	257.6
60°	177.5
62.5°	131.6
65°	97.4
67.5°	74.4
70°	51.5
72.5°	40.1
75°	28.6
77.5°	17.1
80°	11.5
82.5°	5.8
85°	5.8
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)