

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204040

Luminaire Tested: **LE_6B10D010 EC6B10209030 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204040
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10209030 6LBNMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 819.1 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204040

CATALOG NUMBER: LE_6B10D010 EC6B10209030 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204040

CATALOG NUMBER: LE_6B10D010 EC6B10209030 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90				90
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81				81
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73				73
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66				66
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61				61
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56				56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51				51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47				47
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44				44
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41				41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204040

CATALOG NUMBER: LE_6B10D010 EC6B10209030 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.4	7.6
10°-20°	165.3	20.2
20°-30°	220.7	27.0
30°-40°	178.1	21.7
40°-50°	85.4	10.4
50°-60°	50.6	6.2
60°-70°	33.6	4.1
70°-80°	18.0	2.2
80°-90°	4.9	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	448.4	54.8
0°-40°	626.5	76.5
0°-60°	762.5	93.1
0°-90°	819.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	819.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	672	
5°	664	62
15°	588	165
25°	483	221
35°	285	178
45°	106	85
55°	56	51
65°	34	34
75°	17	18
85°	4	5
90°	0	



TEST NUMBER: P204040

CATALOG NUMBER: LE_6B10D010 EC6B10209030 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	671.8
2.5°	671.8
5°	663.9
7.5°	650.9
10°	632.6
12.5°	613.1
15°	588.4
17.5°	565.0
20°	539.0
22.5°	511.6
25°	483.0
27.5°	453.0
30°	410.1
32.5°	350.2
35°	285.1
37.5°	225.2
40°	174.5
42.5°	135.4
45°	105.5
47.5°	83.4
50°	70.2
52.5°	62.5
55°	56.0
57.5°	50.8
60°	44.2
62.5°	39.0
65°	33.9
67.5°	28.6
70°	24.8
72.5°	20.9
75°	16.9
77.5°	13.0
80°	10.4
82.5°	7.8
85°	3.9
87.5°	1.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)