

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204665

Luminaire Tested: **LE\_6B10D010 EC6B10209730 6LBPSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204665  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B10D010 EC6B10209730 6LBPSMW1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1076.9 lumens  
Efficiency: N/A  
Efficacy: 108.8 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204665

CATALOG NUMBER: LE\_6B10D010 EC6B10209730 6LBPSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204665

CATALOG NUMBER: LE\_6B10D010 EC6B10209730 6LBPSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    | 20 |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    |    | 0  |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0  |     |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |    | 100 |
| 1   | 110 | 106 | 102 | 99  | 107 | 104 | 100 | 97  | 99  | 97  | 94  | 96  | 93  | 91  | 92  | 90  | 88  | 86  |    |    |    | 86  |
| 2   | 101 | 93  | 87  | 82  | 98  | 92  | 86  | 81  | 88  | 83  | 79  | 85  | 81  | 77  | 82  | 79  | 76  | 74  |    |    |    | 74  |
| 3   | 93  | 83  | 75  | 69  | 90  | 81  | 74  | 69  | 78  | 72  | 67  | 76  | 70  | 66  | 73  | 69  | 65  | 63  |    |    |    | 63  |
| 4   | 85  | 74  | 66  | 59  | 83  | 72  | 65  | 59  | 70  | 63  | 58  | 68  | 62  | 57  | 66  | 61  | 56  | 54  |    |    |    | 54  |
| 5   | 78  | 66  | 58  | 51  | 76  | 65  | 57  | 51  | 63  | 56  | 51  | 61  | 55  | 50  | 59  | 54  | 49  | 47  |    |    |    | 47  |
| 6   | 73  | 60  | 51  | 45  | 71  | 59  | 51  | 45  | 57  | 50  | 44  | 55  | 49  | 44  | 54  | 48  | 44  | 42  |    |    |    | 42  |
| 7   | 67  | 54  | 46  | 40  | 66  | 54  | 46  | 40  | 52  | 45  | 40  | 51  | 44  | 39  | 49  | 43  | 39  | 37  |    |    |    | 37  |
| 8   | 63  | 50  | 41  | 36  | 61  | 49  | 41  | 36  | 48  | 41  | 35  | 46  | 40  | 35  | 45  | 39  | 35  | 33  |    |    |    | 33  |
| 9   | 59  | 46  | 38  | 32  | 57  | 45  | 37  | 32  | 44  | 37  | 32  | 43  | 36  | 32  | 42  | 36  | 32  | 30  |    |    |    | 30  |
| 10  | 55  | 42  | 34  | 29  | 54  | 42  | 34  | 29  | 41  | 34  | 29  | 40  | 33  | 29  | 39  | 33  | 29  | 27  |    |    |    | 27  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204665

CATALOG NUMBER: LE\_6B10D010 EC6B10209730 6LBPSMW1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 41.1   | 3.8       |
| 10°-20°   | 117.2  | 10.9      |
| 20°-30°   | 176.5  | 16.4      |
| 30°-40°   | 210.0  | 19.5      |
| 40°-50°   | 209.7  | 19.5      |
| 50°-60°   | 170.5  | 15.8      |
| 60°-70°   | 104.9  | 9.7       |
| 70°-80°   | 40.6   | 3.8       |
| 80°-90°   | 6.5    | 0.6       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 334.8  | 31.1      |
| 0°-40°    | 544.8  | 50.6      |
| 0°-60°    | 924.9  | 85.9      |
| 0°-90°    | 1076.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1076.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 434 |      |
| 5°  | 433 | 41   |
| 15° | 416 | 117  |
| 25° | 384 | 176  |
| 35° | 336 | 210  |
| 45° | 272 | 210  |
| 55° | 191 | 170  |
| 65° | 105 | 105  |
| 75° | 37  | 41   |
| 85° | 5   | 6    |
| 90° | 0   |      |



TEST NUMBER: P204665

CATALOG NUMBER: LE\_6B10D010 EC6B10209730 6LBPSMW1

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 433.9 |
| 2.5°  | 434.5 |
| 5°    | 432.6 |
| 7.5°  | 430.1 |
| 10°   | 426.9 |
| 12.5° | 421.1 |
| 15°   | 416.0 |
| 17.5° | 408.4 |
| 20°   | 400.1 |
| 22.5° | 392.4 |
| 25°   | 384.1 |
| 27.5° | 372.6 |
| 30°   | 361.1 |
| 32.5° | 350.4 |
| 35°   | 336.2 |
| 37.5° | 321.0 |
| 40°   | 306.9 |
| 42.5° | 289.8 |
| 45°   | 272.5 |
| 47.5° | 254.0 |
| 50°   | 234.1 |
| 52.5° | 213.8 |
| 55°   | 190.8 |
| 57.5° | 168.5 |
| 60°   | 146.8 |
| 62.5° | 125.8 |
| 65°   | 105.2 |
| 67.5° | 86.1  |
| 70°   | 68.2  |
| 72.5° | 51.6  |
| 75°   | 37.0  |
| 77.5° | 24.2  |
| 80°   | 14.6  |
| 82.5° | 8.9   |
| 85°   | 5.1   |
| 87.5° | 2.5   |
| 90°   | 0.0   |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)