

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204966

Luminaire Tested: **LE_6B10D010 EC6B10208040 6LBCS1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204966
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10208040 6LBCS1MMS
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1415.7 lumens
Efficiency: N/A
Efficacy: 143.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204966

CATALOG NUMBER: LE_6B10D010 EC6B10208040 6LBCS1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P204966

CATALOG NUMBER: LE_6B10D010 EC6B10208040 6LBCS1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88				88
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76				76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65				65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57				57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50				50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44				44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40				40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36				36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32				32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29				29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204966

CATALOG NUMBER: LE_6B10D010 EC6B10208040 6LBCS1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.3	4.3
10°-20°	171.9	12.1
20°-30°	251.1	17.7
30°-40°	287.2	20.3
40°-50°	276.0	19.5
50°-60°	213.1	15.1
60°-70°	119.0	8.4
70°-80°	34.6	2.4
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	484.3	34.2
0°-40°	771.5	54.5
0°-60°	1260.6	89.0
0°-90°	1415.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1415.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	650	
5°	645	61
15°	610	172
25°	546	251
35°	460	287
45°	360	276
55°	239	213
65°	119	119
75°	30	35
85°	1	2
90°	0	



TEST NUMBER: P204966

CATALOG NUMBER: LE_6B10D010 EC6B10208040 6LBCS1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	650.1
2.5°	650.1
5°	644.6
7.5°	641.9
10°	632.8
12.5°	621.8
15°	609.9
17.5°	597.9
20°	580.5
22.5°	566.8
25°	545.8
27.5°	524.6
30°	503.6
32.5°	482.5
35°	459.6
37.5°	436.8
40°	410.2
42.5°	386.4
45°	359.9
47.5°	329.6
50°	301.2
52.5°	270.1
55°	239.0
57.5°	207.0
60°	176.8
62.5°	146.5
65°	119.0
67.5°	93.4
70°	69.6
72.5°	48.5
75°	30.2
77.5°	15.6
80°	5.5
82.5°	1.9
85°	0.9
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)