

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204863

Luminaire Tested: **LE_6B10D010 EC6B10208040 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204863
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10208040 6LBCSMB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1277.5 lumens
Efficiency: N/A
Efficacy: 129.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204863

CATALOG NUMBER: LE_6B10D010 EC6B10208040 6LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P204863

CATALOG NUMBER: LE_6B10D010 EC6B10208040 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88																			
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75																			
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65																			
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56																			
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49																			
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43																			
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39																			
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35																			
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31																			
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204863

CATALOG NUMBER: LE_6B10D010 EC6B10208040 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.0	4.0
10°-20°	145.4	11.4
20°-30°	218.5	17.1
30°-40°	259.3	20.3
40°-50°	256.5	20.1
50°-60°	201.5	15.8
60°-70°	113.0	8.8
70°-80°	31.8	2.5
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	414.9	32.5
0°-40°	674.2	52.8
0°-60°	1132.2	88.6
0°-90°	1277.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1277.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	539	
5°	538	51
15°	516	145
25°	474	219
35°	416	259
45°	334	257
55°	227	202
65°	113	113
75°	28	32
85°	0	0
90°	0	



TEST NUMBER: P204863

CATALOG NUMBER: LE_6B10D010 EC6B10208040 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	539.4
2.5°	537.6
5°	538.5
7.5°	533.9
10°	528.4
12.5°	522.0
15°	515.6
17.5°	507.4
20°	496.4
22.5°	485.4
25°	474.4
27.5°	462.5
30°	446.9
32.5°	431.4
35°	415.8
37.5°	397.5
40°	376.4
42.5°	356.2
45°	334.2
47.5°	309.5
50°	283.9
52.5°	254.6
55°	227.1
57.5°	196.0
60°	166.6
62.5°	140.1
65°	112.6
67.5°	88.9
70°	66.0
72.5°	44.9
75°	27.5
77.5°	13.8
80°	3.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)