

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205474

Luminaire Tested: **LE\_6B10D010 EC6B10208040 6LBMGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205474  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B10D010 EC6B10208040 6LBMGPH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 768.0 lumens  
Efficiency: N/A  
Efficacy: 77.6 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205474

CATALOG NUMBER: LE\_6B10D010 EC6B10208040 6LBMGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P205474

CATALOG NUMBER: LE\_6B10D010 EC6B10208040 6LBMGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																																				
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86																																				
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79																																				
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73																																				
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68																																				
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63																																				
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59																																				
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55																																				
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51																																				
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48																																				

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205474

CATALOG NUMBER: LE\_6B10D010 EC6B10208040 6LBMGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.5	9.6
10°-20°	190.8	24.8
20°-30°	243.1	31.7
30°-40°	171.8	22.4
40°-50°	62.7	8.2
50°-60°	17.4	2.3
60°-70°	6.3	0.8
70°-80°	2.2	0.3
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	507.4	66.1
0°-40°	679.2	88.4
0°-60°	759.3	98.9
0°-90°	768.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	768.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	800	
5°	786	74
15°	679	191
25°	540	243
35°	273	172
45°	76	63
55°	19	17
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P205474

CATALOG NUMBER: LE\_6B10D010 EC6B10208040 6LBMGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	800.2
2.5°	797.2
5°	786.4
7.5°	764.6
10°	741.4
12.5°	710.4
15°	679.4
17.5°	648.4
20°	617.2
22.5°	580.1
25°	539.8
27.5°	483.9
30°	421.9
32.5°	347.4
35°	273.0
37.5°	207.9
40°	152.0
42.5°	110.1
45°	76.0
47.5°	51.1
50°	34.1
52.5°	23.2
55°	18.6
57.5°	14.0
60°	10.9
62.5°	7.8
65°	6.2
67.5°	4.6
70°	3.1
72.5°	3.1
75°	1.5
77.5°	1.5
80°	1.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)