

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205217

Luminaire Tested: **LE\_6B40D010 EC6B30508030 6LBWLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205217  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B40D010 EC6B30508030 6LBWL1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57  
W DL3-44.71 W DLE-39.33 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5277.1 lumens  
Efficiency: N/A  
Efficacy: 126.2 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205217

CATALOG NUMBER: LE\_6B40D010 EC6B30508030 6LBWL11

### Luminous Intensity Polar Plot





TEST NUMBER: P205217

CATALOG NUMBER: LE\_6B40D010 EC6B30508030 6LBWLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92			
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76			
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69			
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63			
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205217

CATALOG NUMBER: LE\_6B40D010 EC6B30508030 6LBWLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	318.0	6.0
10°-20°	955.9	18.1
20°-30°	1441.0	27.3
30°-40°	1474.9	27.9
40°-50°	859.2	16.3
50°-60°	197.4	3.7
60°-70°	24.3	0.5
70°-80°	6.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2714.9	51.4
0°-40°	4189.8	79.4
0°-60°	5246.4	99.4
0°-90°	5277.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5277.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3297	
5°	3314	318
15°	3386	956
25°	3159	1441
35°	2393	1475
45°	1107	859
55°	192	197
65°	18	24
75°	6	6
85°	0	0
90°	0	



TEST NUMBER: P205217

CATALOG NUMBER: LE\_6B40D010 EC6B30508030 6LBWLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3296.6
2.5°	3290.6
5°	3314.5
7.5°	3338.5
10°	3368.4
12.5°	3374.4
15°	3386.4
17.5°	3374.4
20°	3344.5
22.5°	3248.8
25°	3159.0
27.5°	3015.4
30°	2829.9
32.5°	2638.5
35°	2393.1
37.5°	2118.0
40°	1812.9
42.5°	1471.8
45°	1106.9
47.5°	771.8
50°	508.5
52.5°	323.1
55°	191.5
57.5°	101.8
60°	53.9
62.5°	29.9
65°	18.0
67.5°	18.0
70°	12.0
72.5°	6.0
75°	6.0
77.5°	6.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)