

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202492

Luminaire Tested: **LE\_6B10D010 EC6B10208040 6LBSWMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202492  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B10D010 EC6B10208040 6LBSWMH1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1446.6 lumens  
Efficiency: N/A  
Efficacy: 146.1 lumens/watt  
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202492

CATALOG NUMBER: LE\_6B10D010 EC6B10208040 6LBSWMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P202492

CATALOG NUMBER: LE\_6B10D010 EC6B10208040 6LBSWMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88				88
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	81	79	77				77
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67				67
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59				59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52				52
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47				47
7	70	58	50	45	69	57	50	45	56	49	44	55	48	44	53	48	44	42				42
8	66	54	46	40	64	53	45	40	52	45	40	50	44	40	49	44	40	38				38
9	62	49	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35				35
10	58	46	39	34	57	45	38	34	45	38	34	44	38	33	43	37	33	32				32

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202492

CATALOG NUMBER: LE\_6B10D010 EC6B10208040 6LBSWMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	77.4	5.4
10°-20°	202.3	14.0
20°-30°	268.3	18.5
30°-40°	286.1	19.8
40°-50°	267.5	18.5
50°-60°	204.0	14.1
60°-70°	110.9	7.7
70°-80°	29.8	2.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	548.0	37.9
0°-40°	834.1	57.7
0°-60°	1305.5	90.2
0°-90°	1446.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1446.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	836	
5°	825	77
15°	721	202
25°	584	268
35°	457	286
45°	348	267
55°	230	204
65°	111	111
75°	26	30
85°	0	0
90°	0	



TEST NUMBER: P202492

CATALOG NUMBER: LE\_6B10D010 EC6B10208040 6LBSWMH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	836.5
2.5°	833.9
5°	825.0
7.5°	806.4
10°	785.1
12.5°	755.0
15°	721.2
17.5°	687.6
20°	651.2
22.5°	616.8
25°	584.0
27.5°	549.4
30°	516.6
32.5°	484.8
35°	457.2
37.5°	429.8
40°	401.4
42.5°	375.8
45°	348.2
47.5°	318.1
50°	289.8
52.5°	259.6
55°	229.5
57.5°	196.8
60°	166.6
62.5°	138.2
65°	110.8
67.5°	86.0
70°	62.9
72.5°	43.4
75°	25.8
77.5°	11.5
80°	2.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)