

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204195

Luminaire Tested: **LE\_6B40D010 EC6B30509030 6LBSH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204195  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B40D010 EC6B30509030 6LBSH1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57  
W DL3-44.71 W DLE-39.33 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4644.5 lumens  
Efficiency: N/A  
Efficacy: 111.1 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204195

CATALOG NUMBER: LE\_6B40D010 EC6B30509030 6LBSH1

### Luminous Intensity Polar Plot





TEST NUMBER: P204195

CATALOG NUMBER: LE\_6B40D010 EC6B30509030 6LBSH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF  | 20  |     |     |     |     |     |     |     |     | 20  |     |     |     |     |     |     |     |     | 20 |    |   |  |  |  |  |  |  | 20 |  |  |  |  |  |  |  |  |   |
| RC  | 80  |     |     |     |     |     |     |     |     | 50  |     |     |     |     |     |     |     |     | 30 |    |   |  |  |  |  |  |  | 10 |  |  |  |  |  |  |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 1   | 111 | 107 | 104 | 101 | 108 | 105 | 102 | 99  | 101 | 98  | 96  | 97  | 95  | 93  | 93  | 92  | 90  | 88  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 2   | 102 | 96  | 90  | 85  | 100 | 94  | 88  | 84  | 90  | 86  | 82  | 87  | 83  | 80  | 84  | 81  | 79  | 77  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 3   | 95  | 85  | 78  | 73  | 92  | 84  | 77  | 72  | 81  | 75  | 71  | 78  | 74  | 70  | 76  | 72  | 69  | 67  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 4   | 87  | 77  | 69  | 63  | 85  | 75  | 68  | 63  | 73  | 67  | 62  | 71  | 65  | 61  | 69  | 64  | 60  | 58  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 5   | 81  | 69  | 61  | 55  | 79  | 68  | 61  | 55  | 66  | 60  | 55  | 64  | 59  | 54  | 63  | 58  | 53  | 51  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 6   | 75  | 63  | 55  | 49  | 73  | 62  | 54  | 49  | 60  | 54  | 49  | 59  | 53  | 48  | 57  | 52  | 48  | 46  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 7   | 70  | 58  | 50  | 44  | 68  | 57  | 49  | 44  | 55  | 49  | 44  | 54  | 48  | 43  | 53  | 47  | 43  | 41  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 8   | 65  | 53  | 45  | 40  | 64  | 52  | 45  | 40  | 51  | 44  | 39  | 50  | 44  | 39  | 49  | 43  | 39  | 37  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 9   | 61  | 49  | 41  | 36  | 60  | 48  | 41  | 36  | 47  | 40  | 36  | 46  | 40  | 36  | 45  | 40  | 35  | 34  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 10  | 58  | 45  | 38  | 33  | 56  | 45  | 38  | 33  | 44  | 37  | 33  | 43  | 37  | 33  | 42  | 37  | 33  | 31  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204195

CATALOG NUMBER: LE\_6B40D010 EC6B30509030 6LBSH1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 227.5  | 4.9       |
| 10°-20°   | 618.4  | 13.3      |
| 20°-30°   | 858.8  | 18.5      |
| 30°-40°   | 937.2  | 20.2      |
| 40°-50°   | 874.3  | 18.8      |
| 50°-60°   | 663.6  | 14.3      |
| 60°-70°   | 363.3  | 7.8       |
| 70°-80°   | 100.0  | 2.2       |
| 80°-90°   | 1.4    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1704.8 | 36.7      |
| 0°-40°    | 2642.0 | 56.9      |
| 0°-60°    | 4179.9 | 90.0      |
| 0°-90°    | 4644.5 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 4644.5 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2429 |      |
| 5°  | 2409 | 228  |
| 15° | 2204 | 618  |
| 25° | 1867 | 859  |
| 35° | 1498 | 937  |
| 45° | 1135 | 874  |
| 55° | 742  | 664  |
| 65° | 363  | 363  |
| 75° | 87   | 100  |
| 85° | 0    | 1    |
| 90° | 0    |      |



TEST NUMBER: P204195

CATALOG NUMBER: LE\_6B40D010 EC6B30509030 6LBSH1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 2429.1 |
| 2.5°  | 2429.1 |
| 5°    | 2408.6 |
| 7.5°  | 2378.0 |
| 10°   | 2332.0 |
| 12.5° | 2270.6 |
| 15°   | 2204.1 |
| 17.5° | 2122.2 |
| 20°   | 2045.5 |
| 22.5° | 1953.5 |
| 25°   | 1866.6 |
| 27.5° | 1779.6 |
| 30°   | 1682.5 |
| 32.5° | 1590.4 |
| 35°   | 1498.4 |
| 37.5° | 1406.4 |
| 40°   | 1319.4 |
| 42.5° | 1227.4 |
| 45°   | 1135.2 |
| 47.5° | 1043.2 |
| 50°   | 941.0  |
| 52.5° | 843.8  |
| 55°   | 741.5  |
| 57.5° | 644.4  |
| 60°   | 547.2  |
| 62.5° | 450.0  |
| 65°   | 363.1  |
| 67.5° | 281.2  |
| 70°   | 209.6  |
| 72.5° | 143.2  |
| 75°   | 86.9   |
| 77.5° | 40.9   |
| 80°   | 10.2   |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)