

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203582

Luminaire Tested: **LE\_6B40D010 EC6B30509730 6LBMMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203582  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B40D010 EC6B30509730 6LBMMW1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57  
W DL3-44.71 W DLE-39.33 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3126.3 lumens  
Efficiency: N/A  
Efficacy: 74.8 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.97  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203582

CATALOG NUMBER: LE\_6B40D010 EC6B30509730 6LBMMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P203582

CATALOG NUMBER: LE\_6B40D010 EC6B30509730 6LBMMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203582

CATALOG NUMBER: LE\_6B40D010 EC6B30509730 6LBMMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	215.5	6.9
10°-20°	577.2	18.5
20°-30°	775.0	24.8
30°-40°	635.7	20.3
40°-50°	381.8	12.2
50°-60°	253.7	8.1
60°-70°	170.0	5.4
70°-80°	91.5	2.9
80°-90°	25.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1567.8	50.1
0°-40°	2203.5	70.5
0°-60°	2839.0	90.8
0°-90°	3126.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3126.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2333	
5°	2294	215
15°	2057	577
25°	1708	775
35°	1009	636
45°	483	382
55°	280	254
65°	172	170
75°	86	92
85°	22	26
90°	0	



TEST NUMBER: P203582

CATALOG NUMBER: LE\_6B40D010 EC6B30509730 6LBMMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2332.8
2.5°	2315.5
5°	2294.0
7.5°	2246.5
10°	2190.5
12.5°	2121.5
15°	2056.9
17.5°	1979.2
20°	1901.6
22.5°	1815.4
25°	1707.5
27.5°	1578.2
30°	1405.8
32.5°	1211.6
35°	1009.0
37.5°	836.5
40°	689.9
42.5°	573.5
45°	483.0
47.5°	409.6
50°	357.9
52.5°	314.8
55°	280.2
57.5°	250.1
60°	224.2
62.5°	194.0
65°	172.5
67.5°	146.6
70°	125.0
72.5°	103.5
75°	86.2
77.5°	69.0
80°	51.8
82.5°	38.8
85°	21.5
87.5°	8.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)