

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204051

Luminaire Tested: **LE\_6B15D010 EC6B10209024 6LBNMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204051  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B15D010 EC6B10209024 6LBNMW1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W  
DL3-15.28 W DLE-15.432 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 956.1 lumens  
Efficiency: N/A  
Efficacy: 66.9 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204051

CATALOG NUMBER: LE\_6B15D010 EC6B10209024 6LBNMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204051

CATALOG NUMBER: LE\_6B15D010 EC6B10209024 6LBNMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204051

CATALOG NUMBER: LE\_6B15D010 EC6B10209024 6LBNMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.8	7.6
10°-20°	193.0	20.2
20°-30°	257.7	27.0
30°-40°	207.9	21.7
40°-50°	99.6	10.4
50°-60°	59.1	6.2
60°-70°	39.2	4.1
70°-80°	21.1	2.2
80°-90°	5.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	523.5	54.8
0°-40°	731.4	76.5
0°-60°	890.0	93.1
0°-90°	956.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	956.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	784	
5°	775	73
15°	687	193
25°	564	258
35°	333	208
45°	123	100
55°	65	59
65°	40	39
75°	20	21
85°	4	6
90°	0	



TEST NUMBER: P204051

CATALOG NUMBER: LE\_6B15D010 EC6B10209024 6LBNMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	784.1
2.5°	784.1
5°	775.0
7.5°	759.9
10°	738.5
12.5°	715.8
15°	686.9
17.5°	659.5
20°	629.1
22.5°	597.2
25°	563.8
27.5°	528.9
30°	478.6
32.5°	408.8
35°	332.8
37.5°	262.9
40°	203.6
42.5°	158.0
45°	123.1
47.5°	97.2
50°	82.0
52.5°	73.0
55°	65.4
57.5°	59.2
60°	51.6
62.5°	45.6
65°	39.5
67.5°	33.4
70°	28.9
72.5°	24.4
75°	19.8
77.5°	15.2
80°	12.1
82.5°	9.1
85°	4.5
87.5°	1.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)