

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204977

Luminaire Tested: **LE_6B15D010 EC6B10208030 6LBCS1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204977
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208030 6LBCS1MMS
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1884.8 lumens
Efficiency: N/A
Efficacy: 131.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204977

CATALOG NUMBER: LE_6B15D010 EC6B10208030 6LBCS1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P204977

CATALOG NUMBER: LE_6B15D010 EC6B10208030 6LBCS1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76			76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65			65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50			50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44			44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40			40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36			36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32			32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29			29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204977

CATALOG NUMBER: LE_6B15D010 EC6B10208030 6LBCS1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.6	4.3
10°-20°	228.9	12.1
20°-30°	334.3	17.7
30°-40°	382.4	20.3
40°-50°	367.5	19.5
50°-60°	283.7	15.1
60°-70°	158.4	8.4
70°-80°	46.1	2.4
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	644.7	34.2
0°-40°	1027.1	54.5
0°-60°	1678.3	89.0
0°-90°	1884.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1884.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	866	
5°	858	82
15°	812	229
25°	727	334
35°	612	382
45°	479	367
55°	318	284
65°	158	158
75°	40	46
85°	1	2
90°	0	



TEST NUMBER: P204977

CATALOG NUMBER: LE_6B15D010 EC6B10208030 6LBCS1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	865.5
2.5°	865.5
5°	858.2
7.5°	854.6
10°	842.4
12.5°	827.8
15°	811.9
17.5°	796.0
20°	772.9
22.5°	754.6
25°	726.6
27.5°	698.5
30°	670.5
32.5°	642.5
35°	612.0
37.5°	581.5
40°	546.1
42.5°	514.5
45°	479.1
47.5°	438.9
50°	401.1
52.5°	359.6
55°	318.1
57.5°	275.5
60°	235.2
62.5°	195.0
65°	158.5
67.5°	124.4
70°	92.6
72.5°	64.6
75°	40.2
77.5°	20.8
80°	7.4
82.5°	2.5
85°	1.2
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)