

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205078

Luminaire Tested: **LE_6B15D010 EC6B10208030 6LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205078
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208030 6LBML1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1639.7 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205078

CATALOG NUMBER: LE_6B15D010 EC6B10208030 6LBMLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205078

CATALOG NUMBER: LE_6B15D010 EC6B10208030 6LBMLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205078

CATALOG NUMBER: LE_6B15D010 EC6B10208030 6LBMLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	11.5
10°-20°	470.6	28.7
20°-30°	547.1	33.4
30°-40°	335.0	20.4
40°-50°	83.2	5.1
50°-60°	9.7	0.6
60°-70°	3.6	0.2
70°-80°	1.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1206.8	73.6
0°-40°	1541.8	94.0
0°-60°	1634.7	99.7
0°-90°	1639.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1639.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2052	
5°	2025	189
15°	1689	471
25°	1211	547
35°	524	335
45°	92	83
55°	8	10
65°	4	4
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P205078

CATALOG NUMBER: LE_6B15D010 EC6B10208030 6LBMLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2052.1
2.5°	2050.0
5°	2024.8
7.5°	1970.2
10°	1896.9
12.5°	1800.2
15°	1689.1
17.5°	1569.5
20°	1452.0
22.5°	1334.5
25°	1210.8
27.5°	1068.0
30°	904.4
32.5°	713.4
35°	524.5
37.5°	369.2
40°	251.8
42.5°	157.4
45°	92.4
47.5°	52.5
50°	27.2
52.5°	12.6
55°	8.4
57.5°	6.2
60°	6.2
62.5°	4.2
65°	4.2
67.5°	2.1
70°	2.1
72.5°	2.1
75°	2.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)