

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202503

Luminaire Tested: **LE_6B15D010 EC6B10208030 6LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202503
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208030 6LBSWMH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1925.8 lumens
Efficiency: N/A
Efficacy: 134.7 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202503

CATALOG NUMBER: LE_6B15D010 EC6B10208030 6LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202503

CATALOG NUMBER: LE_6B15D010 EC6B10208030 6LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 111 | 107 | 104 | 101 | 108 | 105 | 102 | 99 | 101 | 98 | 96 | 97 | 95 | 93 | 94 | 92 | 90 | 88 | | | | | | | | | | | | | | | | | | | |
| 2 | 103 | 96 | 90 | 85 | 100 | 94 | 89 | 84 | 91 | 86 | 82 | 87 | 84 | 81 | 84 | 81 | 79 | 77 | | | | | | | | | | | | | | | | | | | |
| 3 | 95 | 86 | 79 | 73 | 92 | 84 | 78 | 73 | 81 | 76 | 71 | 79 | 74 | 70 | 76 | 72 | 69 | 67 | | | | | | | | | | | | | | | | | | | |
| 4 | 88 | 77 | 70 | 64 | 86 | 76 | 69 | 63 | 74 | 67 | 62 | 71 | 66 | 62 | 69 | 65 | 61 | 59 | | | | | | | | | | | | | | | | | | | |
| 5 | 81 | 70 | 62 | 56 | 79 | 69 | 61 | 56 | 67 | 60 | 55 | 65 | 59 | 55 | 63 | 58 | 54 | 52 | | | | | | | | | | | | | | | | | | | |
| 6 | 76 | 64 | 56 | 50 | 74 | 63 | 55 | 50 | 61 | 54 | 49 | 59 | 53 | 49 | 58 | 53 | 48 | 47 | | | | | | | | | | | | | | | | | | | |
| 7 | 70 | 58 | 50 | 45 | 69 | 57 | 50 | 45 | 56 | 49 | 44 | 55 | 48 | 44 | 53 | 48 | 44 | 42 | | | | | | | | | | | | | | | | | | | |
| 8 | 66 | 54 | 46 | 40 | 64 | 53 | 45 | 40 | 52 | 45 | 40 | 50 | 44 | 40 | 49 | 44 | 40 | 38 | | | | | | | | | | | | | | | | | | | |
| 9 | 62 | 49 | 42 | 37 | 61 | 49 | 42 | 37 | 48 | 41 | 37 | 47 | 41 | 36 | 46 | 40 | 36 | 35 | | | | | | | | | | | | | | | | | | | |
| 10 | 58 | 46 | 39 | 34 | 57 | 45 | 38 | 34 | 45 | 38 | 34 | 44 | 38 | 33 | 43 | 37 | 33 | 32 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202503

CATALOG NUMBER: LE_6B15D010 EC6B10208030 6LBSWMH1

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 103.0 | 5.4 |
| 10°-20° | 269.3 | 14.0 |
| 20°-30° | 357.1 | 18.5 |
| 30°-40° | 380.9 | 19.8 |
| 40°-50° | 356.1 | 18.5 |
| 50°-60° | 271.5 | 14.1 |
| 60°-70° | 147.7 | 7.7 |
| 70°-80° | 39.6 | 2.1 |
| 80°-90° | 0.5 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 729.5 | 37.9 |
| 0°-40° | 1110.4 | 57.7 |
| 0°-60° | 1738.0 | 90.2 |
| 0°-90° | 1925.8 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1925.8 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1114 | |
| 5° | 1098 | 103 |
| 15° | 960 | 269 |
| 25° | 777 | 357 |
| 35° | 609 | 381 |
| 45° | 464 | 356 |
| 55° | 306 | 271 |
| 65° | 148 | 148 |
| 75° | 34 | 40 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P202503

CATALOG NUMBER: LE_6B15D010 EC6B10208030 6LBSWMH1

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1113.6 |
| 2.5° | 1110.1 |
| 5° | 1098.4 |
| 7.5° | 1073.5 |
| 10° | 1045.2 |
| 12.5° | 1005.1 |
| 15° | 960.2 |
| 17.5° | 915.5 |
| 20° | 867.1 |
| 22.5° | 821.1 |
| 25° | 777.4 |
| 27.5° | 731.4 |
| 30° | 687.8 |
| 32.5° | 645.2 |
| 35° | 608.8 |
| 37.5° | 572.1 |
| 40° | 534.4 |
| 42.5° | 500.2 |
| 45° | 463.6 |
| 47.5° | 423.5 |
| 50° | 385.8 |
| 52.5° | 345.6 |
| 55° | 305.5 |
| 57.5° | 261.9 |
| 60° | 221.8 |
| 62.5° | 184.0 |
| 65° | 147.5 |
| 67.5° | 114.4 |
| 70° | 83.8 |
| 72.5° | 57.8 |
| 75° | 34.2 |
| 77.5° | 15.4 |
| 80° | 3.5 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)