

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203744

Luminaire Tested: **LE_6B15D010 EC6B10209030 6LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203744
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209030 6LBNWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1054.7 lumens
Efficiency: N/A
Efficacy: 73.8 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203744

CATALOG NUMBER: LE_6B15D010 EC6B10209030 6LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203744

CATALOG NUMBER: LE_6B15D010 EC6B10209030 6LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89			
3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83			
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79			
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74			
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70			
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	67	66			
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63			
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60			
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203744

CATALOG NUMBER: LE_6B15D010 EC6B10209030 6LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.3	16.6
10°-20°	336.8	31.9
20°-30°	306.2	29.0
30°-40°	185.6	17.6
40°-50°	42.3	4.0
50°-60°	5.4	0.5
60°-70°	2.4	0.2
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	818.3	77.6
0°-40°	1003.9	95.2
0°-60°	1051.6	99.7
0°-90°	1054.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1054.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2071	
5°	1952	175
15°	1213	337
25°	664	306
35°	294	186
45°	47	42
55°	5	5
65°	2	2
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203744

CATALOG NUMBER: LE_6B15D010 EC6B10209030 6LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2070.8
2.5°	2045.6
5°	1952.2
7.5°	1801.5
10°	1609.5
12.5°	1410.4
15°	1213.0
17.5°	1033.6
20°	882.9
22.5°	760.9
25°	663.9
27.5°	577.8
30°	493.5
32.5°	394.8
35°	294.2
37.5°	206.4
40°	136.4
42.5°	84.4
45°	46.6
47.5°	21.5
50°	9.0
52.5°	7.1
55°	5.4
57.5°	5.4
60°	3.6
62.5°	3.6
65°	1.8
67.5°	1.8
70°	1.8
72.5°	1.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)