

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204609

Luminaire Tested: **LE_6B40D010 EC6B30509035 6LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204609
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B40D010 EC6B30509035 6LBSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4913.1 lumens
Efficiency: N/A
Efficacy: 117.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204609

CATALOG NUMBER: LE_6B40D010 EC6B30509035 6LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204609

CATALOG NUMBER: LE_6B40D010 EC6B30509035 6LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																																				
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																																				
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																																				
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																																				
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																																				
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																																				
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																																				
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																																				
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																																				
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204609

CATALOG NUMBER: LE_6B40D010 EC6B30509035 6LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.6	3.8
10°-20°	534.6	10.9
20°-30°	805.2	16.4
30°-40°	958.1	19.5
40°-50°	956.3	19.5
50°-60°	777.7	15.8
60°-70°	478.5	9.7
70°-80°	185.4	3.8
80°-90°	29.7	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1527.4	31.1
0°-40°	2485.4	50.6
0°-60°	4219.5	85.9
0°-90°	4913.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4913.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1980	
5°	1974	188
15°	1898	535
25°	1752	805
35°	1534	958
45°	1243	956
55°	870	778
65°	480	479
75°	169	185
85°	23	30
90°	0	



TEST NUMBER: P204609

CATALOG NUMBER: LE_6B40D010 EC6B30509035 6LBSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1979.5
2.5°	1982.4
5°	1973.8
7.5°	1962.0
10°	1947.5
12.5°	1921.2
15°	1898.0
17.5°	1863.1
20°	1825.2
22.5°	1790.2
25°	1752.5
27.5°	1700.1
30°	1647.6
32.5°	1598.1
35°	1534.1
37.5°	1464.2
40°	1400.2
42.5°	1321.6
45°	1243.0
47.5°	1158.6
50°	1068.4
52.5°	975.2
55°	870.4
57.5°	768.5
60°	669.5
62.5°	573.5
65°	480.4
67.5°	393.0
70°	311.5
72.5°	235.8
75°	168.9
77.5°	110.6
80°	67.0
82.5°	40.8
85°	23.2
87.5°	11.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)