

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205088

Luminaire Tested: **LE\_6B15D010 EC6B10209730 6LBMLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205088  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B15D010 EC6B10209730 6LBML1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W  
DL3-15.28 W DLE-15.432 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1223.8 lumens  
Efficiency: N/A  
Efficacy: 85.6 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205088

CATALOG NUMBER: LE\_6B15D010 EC6B10209730 6LBMLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P205088

CATALOG NUMBER: LE\_6B15D010 EC6B10209730 6LBMLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205088

CATALOG NUMBER: LE\_6B15D010 EC6B10209730 6LBMLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.1	11.5
10°-20°	351.3	28.7
20°-30°	408.3	33.4
30°-40°	250.0	20.4
40°-50°	62.1	5.1
50°-60°	7.3	0.6
60°-70°	2.7	0.2
70°-80°	1.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	900.7	73.6
0°-40°	1150.7	94.0
0°-60°	1220.1	99.7
0°-90°	1223.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1223.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1532	
5°	1511	141
15°	1261	351
25°	904	408
35°	392	250
45°	69	62
55°	6	7
65°	3	3
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P205088

CATALOG NUMBER: LE\_6B15D010 EC6B10209730 6LBMLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1531.5
2.5°	1530.0
5°	1511.1
7.5°	1470.4
10°	1415.6
12.5°	1343.6
15°	1260.6
17.5°	1171.4
20°	1083.6
22.5°	996.0
25°	903.5
27.5°	797.1
30°	674.9
32.5°	532.4
35°	391.5
37.5°	275.6
40°	187.9
42.5°	117.5
45°	68.9
47.5°	39.1
50°	20.4
52.5°	9.4
55°	6.2
57.5°	4.8
60°	4.8
62.5°	3.1
65°	3.1
67.5°	1.6
70°	1.6
72.5°	1.6
75°	1.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)