

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205223

Luminaire Tested: **LE\_6B40D010 EC6B30509035 6LBWLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205223  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B40D010 EC6B30509035 6LBWL1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57  
W DL3-44.71 W DLE-39.33 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4571.1 lumens  
Efficiency: N/A  
Efficacy: 109.4 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205223

CATALOG NUMBER: LE\_6B40D010 EC6B30509035 6LBWLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P205223

CATALOG NUMBER: LE\_6B40D010 EC6B30509035 6LBWLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92				92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83				83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76				76
4	93	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	70	69				69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63				63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57				57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52				52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48				48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44				44
10	65	54	47	43	64	53	47	43	52	46	42	51	46	42	51	46	42	41				41

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205223

CATALOG NUMBER: LE\_6B40D010 EC6B30509035 6LBWLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	275.5	6.0
10°-20°	828.1	18.1
20°-30°	1248.2	27.3
30°-40°	1277.6	27.9
40°-50°	744.3	16.3
50°-60°	171.0	3.7
60°-70°	21.0	0.5
70°-80°	5.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2351.8	51.4
0°-40°	3629.4	79.4
0°-60°	4544.8	99.4
0°-90°	4571.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4571.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2856	
5°	2871	275
15°	2934	828
25°	2736	1248
35°	2073	1278
45°	959	744
55°	166	171
65°	16	21
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P205223

CATALOG NUMBER: LE\_6B40D010 EC6B30509035 6LBWLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2855.8
2.5°	2850.5
5°	2871.2
7.5°	2892.0
10°	2917.9
12.5°	2923.1
15°	2933.5
17.5°	2923.1
20°	2897.1
22.5°	2814.2
25°	2736.5
27.5°	2612.1
30°	2451.5
32.5°	2285.6
35°	2073.1
37.5°	1834.8
40°	1570.4
42.5°	1275.0
45°	958.9
47.5°	668.6
50°	440.5
52.5°	279.9
55°	165.9
57.5°	88.1
60°	46.6
62.5°	25.9
65°	15.5
67.5°	15.5
70°	10.4
72.5°	5.1
75°	5.1
77.5°	5.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)