

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205016

Luminaire Tested: **LE_6B40D010 EC6B30508040 6LBCS1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205016
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B40D010 EC6B30508040 6LBCS1MMS
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5563.4 lumens
Efficiency: N/A
Efficacy: 133.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205016

CATALOG NUMBER: LE_6B40D010 EC6B30508040 6LBCS1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P205016

CATALOG NUMBER: LE_6B40D010 EC6B30508040 6LBCS1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88																
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76			76																
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65			65																
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57			57																
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50			50																
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44			44																
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40			40																
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36			36																
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32			32																
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29			29																

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205016

CATALOG NUMBER: LE_6B40D010 EC6B30508040 6LBCS1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	240.8	4.3
10°-20°	675.6	12.1
20°-30°	986.8	17.7
30°-40°	1128.6	20.3
40°-50°	1084.7	19.5
50°-60°	837.5	15.1
60°-70°	467.5	8.4
70°-80°	136.1	2.4
80°-90°	5.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1903.1	34.2
0°-40°	3031.8	54.5
0°-60°	4954.0	89.0
0°-90°	5563.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5563.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2555	
5°	2533	241
15°	2396	676
25°	2145	987
35°	1806	1129
45°	1414	1085
55°	939	838
65°	468	467
75°	119	136
85°	4	6
90°	0	



TEST NUMBER: P205016

CATALOG NUMBER: LE_6B40D010 EC6B30508040 6LBCS1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2554.9
2.5°	2554.9
5°	2533.2
7.5°	2522.5
10°	2486.5
12.5°	2443.2
15°	2396.5
17.5°	2349.8
20°	2281.4
22.5°	2227.4
25°	2144.6
27.5°	2061.9
30°	1979.1
32.5°	1896.4
35°	1806.4
37.5°	1716.4
40°	1612.1
42.5°	1518.5
45°	1414.1
47.5°	1295.4
50°	1183.9
52.5°	1061.5
55°	939.1
57.5°	813.2
60°	694.5
62.5°	575.8
65°	467.8
67.5°	367.0
70°	273.5
72.5°	190.8
75°	118.8
77.5°	61.1
80°	21.6
82.5°	7.2
85°	3.6
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)