

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205392

Luminaire Tested: **LE_6B15D010 EC6B10209730 6LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205392
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209730 6LBSLI1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1474.5 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205392

CATALOG NUMBER: LE_6B15D010 EC6B10209730 6LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205392

CATALOG NUMBER: LE_6B15D010 EC6B10209730 6LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89				89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77				77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68				68
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60				60
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53				53
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47				47
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43				43
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39				39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36				36
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33				33

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205392

CATALOG NUMBER: LE_6B15D010 EC6B10209730 6LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.7	5.8
10°-20°	218.3	14.8
20°-30°	278.4	18.9
30°-40°	288.7	19.6
40°-50°	266.0	18.0
50°-60°	200.1	13.6
60°-70°	108.0	7.3
70°-80°	29.0	2.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	582.4	39.5
0°-40°	871.0	59.1
0°-60°	1337.1	90.7
0°-90°	1474.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1474.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	930	
5°	916	86
15°	778	218
25°	605	278
35°	460	289
45°	346	266
55°	224	200
65°	108	108
75°	25	29
85°	0	0
90°	0	



TEST NUMBER: P205392

CATALOG NUMBER: LE_6B15D010 EC6B10209730 6LBSLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	930.5
2.5°	927.4
5°	916.4
7.5°	896.0
10°	860.0
12.5°	824.0
15°	778.5
17.5°	736.2
20°	692.4
22.5°	647.0
25°	604.6
27.5°	563.9
30°	526.4
32.5°	491.9
35°	460.5
37.5°	430.8
40°	402.6
42.5°	372.9
45°	346.1
47.5°	316.4
50°	286.6
52.5°	255.4
55°	224.0
57.5°	192.6
60°	162.9
62.5°	134.8
65°	108.1
67.5°	83.0
70°	61.1
72.5°	42.2
75°	25.1
77.5°	11.0
80°	3.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)