

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202719

Luminaire Tested: **LE\_6B15D010 EC6B10209730 6LBWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202719  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B15D010 EC6B10209730 6LBWH1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W  
DL3-15.28 W DLE-15.432 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1209.7 lumens  
Efficiency: N/A  
Efficacy: 84.6 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202719

CATALOG NUMBER: LE\_6B15D010 EC6B10209730 6LBWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P202719

CATALOG NUMBER: LE\_6B15D010 EC6B10209730 6LBWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202719

CATALOG NUMBER: LE\_6B15D010 EC6B10209730 6LBWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	70.5	5.8
10°-20°	200.0	16.5
20°-30°	293.2	24.2
30°-40°	305.1	25.2
40°-50°	211.1	17.5
50°-60°	91.9	7.6
60°-70°	28.2	2.3
70°-80°	8.5	0.7
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	563.6	46.6
0°-40°	868.8	71.8
0°-60°	1171.8	96.9
0°-90°	1209.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1209.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	746	
5°	743	70
15°	710	200
25°	641	293
35°	494	305
45°	273	211
55°	99	92
65°	27	28
75°	8	8
85°	2	1
90°	0	



TEST NUMBER: P202719

CATALOG NUMBER: LE\_6B15D010 EC6B10209730 6LBWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	746.1
2.5°	747.6
5°	743.0
7.5°	736.8
10°	728.9
12.5°	721.0
15°	710.1
17.5°	696.0
20°	680.2
22.5°	663.0
25°	641.1
27.5°	612.9
30°	576.9
32.5°	539.2
35°	493.8
37.5°	443.6
40°	385.6
42.5°	327.6
45°	272.8
47.5°	221.0
50°	175.5
52.5°	133.2
55°	98.8
57.5°	70.5
60°	48.6
62.5°	36.0
65°	26.6
67.5°	20.4
70°	14.1
72.5°	11.0
75°	7.9
77.5°	4.8
80°	3.1
82.5°	1.6
85°	1.6
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)