

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204875

Luminaire Tested: **LE_6B15D010 EC6B10208040 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204875
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208040 6LBCSMB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1761.9 lumens
Efficiency: N/A
Efficacy: 123.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204875

CATALOG NUMBER: LE_6B15D010 EC6B10208040 6LBCSMB1

Luminous Intensity Polar Plot






TEST NUMBER: P204875

CATALOG NUMBER: LE_6B15D010 EC6B10208040 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88			88
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			75
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65			65
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56			56
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49			49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43			43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39			39
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35			35
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31			31
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28			28

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204875

CATALOG NUMBER: LE_6B15D010 EC6B10208040 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.4	4.0
10°-20°	200.5	11.4
20°-30°	301.4	17.1
30°-40°	357.6	20.3
40°-50°	353.9	20.1
50°-60°	277.9	15.8
60°-70°	155.8	8.8
70°-80°	43.8	2.5
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	572.2	32.5
0°-40°	929.8	52.8
0°-60°	1561.6	88.6
0°-90°	1761.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1761.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	744	
5°	743	70
15°	711	200
25°	654	301
35°	574	358
45°	461	354
55°	313	278
65°	155	156
75°	38	44
85°	0	1
90°	0	



TEST NUMBER: P204875

CATALOG NUMBER: LE_6B15D010 EC6B10208040 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	744.0
2.5°	741.5
5°	742.8
7.5°	736.4
10°	728.9
12.5°	720.0
15°	711.1
17.5°	699.8
20°	684.6
22.5°	669.5
25°	654.2
27.5°	637.9
30°	616.4
32.5°	594.9
35°	573.5
37.5°	548.2
40°	519.1
42.5°	491.4
45°	461.0
47.5°	427.0
50°	391.6
52.5°	351.1
55°	313.2
57.5°	270.2
60°	229.9
62.5°	193.2
65°	155.4
67.5°	122.5
70°	91.0
72.5°	61.9
75°	37.9
77.5°	19.0
80°	5.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)