

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204191

Luminaire Tested: **LE_6B40D010 EC6B30508040 6LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204191
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B40D010 EC6B30508040 6LBSH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5633.3 lumens
Efficiency: N/A
Efficacy: 134.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204191

CATALOG NUMBER: LE_6B40D010 EC6B30508040 6LBSH1

Luminous Intensity Polar Plot





TEST NUMBER: P204191

CATALOG NUMBER: LE_6B40D010 EC6B30508040 6LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204191

CATALOG NUMBER: LE_6B40D010 EC6B30508040 6LSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.0	4.9
10°-20°	750.1	13.3
20°-30°	1041.7	18.5
30°-40°	1136.7	20.2
40°-50°	1060.4	18.8
50°-60°	804.8	14.3
60°-70°	440.7	7.8
70°-80°	121.2	2.2
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2067.7	36.7
0°-40°	3204.5	56.9
0°-60°	5069.7	90.0
0°-90°	5633.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5633.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2946	
5°	2922	276
15°	2673	750
25°	2264	1042
35°	1817	1137
45°	1377	1060
55°	899	805
65°	440	441
75°	106	121
85°	0	2
90°	0	



TEST NUMBER: P204191

CATALOG NUMBER: LE_6B40D010 EC6B30508040 6LBSH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2946.2
2.5°	2946.2
5°	2921.5
7.5°	2884.2
10°	2828.4
12.5°	2754.0
15°	2673.4
17.5°	2574.1
20°	2481.0
22.5°	2369.4
25°	2264.0
27.5°	2158.5
30°	2040.6
32.5°	1929.0
35°	1817.4
37.5°	1705.8
40°	1600.2
42.5°	1488.6
45°	1377.0
47.5°	1265.4
50°	1141.2
52.5°	1023.4
55°	899.4
57.5°	781.5
60°	663.6
62.5°	545.9
65°	440.4
67.5°	341.1
70°	254.2
72.5°	173.6
75°	105.5
77.5°	49.6
80°	12.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)