

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203637

Luminaire Tested: **LE_6B15D010 EC6B10208040 6LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203637
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208040 6LBNH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1194.2 lumens
Efficiency: N/A
Efficacy: 83.5 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203637

CATALOG NUMBER: LE_6B15D010 EC6B10208040 6LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P203637

CATALOG NUMBER: LE_6B15D010 EC6B10208040 6LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203637

CATALOG NUMBER: LE_6B15D010 EC6B10208040 6LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.7	11.5
10°-20°	328.3	27.5
20°-30°	376.1	31.5
30°-40°	252.7	21.2
40°-50°	72.2	6.0
50°-60°	17.7	1.5
60°-70°	6.7	0.6
70°-80°	2.5	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	842.0	70.5
0°-40°	1094.7	91.7
0°-60°	1184.6	99.2
0°-90°	1194.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1194.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1531	
5°	1487	138
15°	1178	328
25°	821	376
35°	403	253
45°	83	72
55°	20	18
65°	6	7
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P203637

CATALOG NUMBER: LE_6B15D010 EC6B10208040 6LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1530.8
2.5°	1519.9
5°	1487.2
7.5°	1428.5
10°	1356.6
12.5°	1265.1
15°	1178.0
17.5°	1086.6
20°	995.1
22.5°	908.0
25°	820.9
27.5°	740.4
30°	646.8
32.5°	522.6
35°	402.9
37.5°	294.0
40°	202.5
42.5°	132.9
45°	82.8
47.5°	50.1
50°	30.5
52.5°	24.0
55°	19.6
57.5°	15.2
60°	10.9
62.5°	8.8
65°	6.5
67.5°	4.4
70°	4.4
72.5°	2.1
75°	2.1
77.5°	2.1
80°	2.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)