

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203161

Luminaire Tested: **LE_6B40D010 EC6B30508040 6LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203161
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B40D010 EC6B30508040 6LBWMW1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5112.8 lumens
Efficiency: N/A
Efficacy: 122.3 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203161

CATALOG NUMBER: LE_6B40D010 EC6B30508040 6LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203161

CATALOG NUMBER: LE_6B40D010 EC6B30508040 6LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77				77
3	95	86	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68				68
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60				60
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54				54
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49				49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44				44
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40				40
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37				37
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34				34

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203161

CATALOG NUMBER: LE_6B40D010 EC6B30508040 6LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	270.4	5.3
10°-20°	758.3	14.8
20°-30°	1092.6	21.4
30°-40°	1134.4	22.2
40°-50°	838.7	16.4
50°-60°	501.0	9.8
60°-70°	304.4	6.0
70°-80°	166.7	3.3
80°-90°	46.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2121.2	41.5
0°-40°	3255.6	63.7
0°-60°	4595.3	89.9
0°-90°	5112.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5112.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2871	
5°	2852	270
15°	2691	758
25°	2381	1093
35°	1829	1134
45°	1079	839
55°	546	501
65°	304	304
75°	155	167
85°	37	46
90°	0	



TEST NUMBER: P203161

CATALOG NUMBER: LE_6B40D010 EC6B30508040 6LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2871.1
2.5°	2871.1
5°	2852.5
7.5°	2827.8
10°	2790.5
12.5°	2747.1
15°	2691.4
17.5°	2629.4
20°	2567.2
22.5°	2480.5
25°	2381.2
27.5°	2275.9
30°	2139.4
32.5°	2003.0
35°	1829.4
37.5°	1649.5
40°	1451.1
42.5°	1258.9
45°	1079.0
47.5°	917.8
50°	775.1
52.5°	651.1
55°	545.8
57.5°	465.1
60°	396.9
62.5°	347.2
65°	303.9
67.5°	266.6
70°	229.5
72.5°	192.2
75°	155.0
77.5°	124.0
80°	93.0
82.5°	68.2
85°	37.2
87.5°	18.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)