

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202504

Luminaire Tested: **LE_6B15D010 EC6B10208040 6LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202504
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208040 6LBSWMH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1995.2 lumens
Efficiency: N/A
Efficacy: 139.5 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202504

CATALOG NUMBER: LE_6B15D010 EC6B10208040 6LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202504

CATALOG NUMBER: LE_6B15D010 EC6B10208040 6LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	81	79	77			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67			
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47			
7	70	58	50	45	69	57	50	45	56	49	44	55	48	44	53	48	44	42			
8	66	54	46	40	64	53	45	40	52	45	40	50	44	40	49	44	40	38			
9	62	49	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35			
10	58	46	39	34	57	45	38	34	45	38	34	44	38	33	43	37	33	32			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202504

CATALOG NUMBER: LE_6B15D010 EC6B10208040 6LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.7	5.4
10°-20°	279.0	14.0
20°-30°	370.0	18.5
30°-40°	394.6	19.8
40°-50°	368.9	18.5
50°-60°	281.3	14.1
60°-70°	153.0	7.7
70°-80°	41.1	2.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	755.8	37.9
0°-40°	1150.4	57.7
0°-60°	1800.7	90.2
0°-90°	1995.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1995.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1154	
5°	1138	107
15°	995	279
25°	805	370
35°	631	395
45°	480	369
55°	316	281
65°	153	153
75°	36	41
85°	0	0
90°	0	



TEST NUMBER: P202504

CATALOG NUMBER: LE_6B15D010 EC6B10208040 6LBSWMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1153.8
2.5°	1150.1
5°	1137.9
7.5°	1112.2
10°	1082.9
12.5°	1041.4
15°	994.9
17.5°	948.4
20°	898.4
22.5°	850.6
25°	805.4
27.5°	757.8
30°	712.5
32.5°	668.5
35°	630.6
37.5°	592.8
40°	553.6
42.5°	518.2
45°	480.4
47.5°	438.8
50°	399.6
52.5°	358.1
55°	316.5
57.5°	271.4
60°	229.8
62.5°	190.6
65°	152.8
67.5°	118.5
70°	86.8
72.5°	59.9
75°	35.5
77.5°	15.9
80°	3.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)