

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205123

Luminaire Tested: **LE\_6B40D010 EC6B30509040 6LBMLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205123  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B40D010 EC6B30509040 6LBML1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57  
W DL3-44.71 W DLE-39.33 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4054.6 lumens  
Efficiency: N/A  
Efficacy: 97.0 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205123

CATALOG NUMBER: LE\_6B40D010 EC6B30509040 6LBMLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P205123

CATALOG NUMBER: LE\_6B40D010 EC6B30509040 6LBMLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94																			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82																			
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76																			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71																			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63																			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205123

CATALOG NUMBER: LE\_6B40D010 EC6B30509040 6LBMLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	467.4	11.5
10°-20°	1163.7	28.7
20°-30°	1352.8	33.4
30°-40°	828.4	20.4
40°-50°	205.7	5.1
50°-60°	24.1	0.6
60°-70°	9.0	0.2
70°-80°	3.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2984.0	73.6
0°-40°	3812.4	94.0
0°-60°	4042.2	99.7
0°-90°	4054.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4054.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5074	
5°	5007	467
15°	4176	1164
25°	2994	1353
35°	1297	828
45°	228	206
55°	21	24
65°	10	9
75°	5	3
85°	0	0
90°	0	



TEST NUMBER: P205123

CATALOG NUMBER: LE\_6B40D010 EC6B30509040 6LBMLI1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5074.1
2.5°	5068.9
5°	5006.6
7.5°	4871.8
10°	4690.1
12.5°	4451.5
15°	4176.5
17.5°	3880.8
20°	3590.2
22.5°	3299.8
25°	2993.6
27.5°	2640.9
30°	2236.1
32.5°	1764.0
35°	1297.0
37.5°	913.1
40°	622.6
42.5°	389.1
45°	228.2
47.5°	129.8
50°	67.5
52.5°	31.1
55°	20.8
57.5°	15.6
60°	15.6
62.5°	10.4
65°	10.4
67.5°	5.2
70°	5.2
72.5°	5.2
75°	5.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)