

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203373

Luminaire Tested: **LE\_6B40D010 EC6B30509040 6LBMWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203373  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B40D010 EC6B30509040 6LBMWH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57  
W DL3-44.71 W DLE-39.33 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3577.0 lumens  
Efficiency: N/A  
Efficacy: 85.6 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203373

CATALOG NUMBER: LE\_6B40D010 EC6B30509040 6LBMWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P203373

CATALOG NUMBER: LE\_6B40D010 EC6B30509040 6LBMWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87		
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81		
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76		
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71		
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66		
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62		
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58		
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55		
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203373

CATALOG NUMBER: LE\_6B40D010 EC6B30509040 6LBMWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	407.9	11.4
10°-20°	1001.5	28.0
20°-30°	1158.8	32.4
30°-40°	740.7	20.7
40°-50°	210.0	5.9
50°-60°	37.5	1.0
60°-70°	15.3	0.4
70°-80°	5.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2568.2	71.8
0°-40°	3308.9	92.5
0°-60°	3556.4	99.4
0°-90°	3577.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3577.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4462	
5°	4383	408
15°	3592	1002
25°	2557	1159
35°	1169	741
45°	244	210
55°	35	38
65°	15	15
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P203373

CATALOG NUMBER: LE\_6B40D010 EC6B30509040 6LBMWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4462.2
2.5°	4457.2
5°	4382.6
7.5°	4248.4
10°	4059.4
12.5°	3840.5
15°	3591.8
17.5°	3333.0
20°	3079.4
22.5°	2830.6
25°	2557.0
27.5°	2258.5
30°	1925.2
32.5°	1552.1
35°	1169.0
37.5°	845.8
40°	587.0
42.5°	388.0
45°	243.8
47.5°	144.2
50°	84.6
52.5°	49.8
55°	34.9
57.5°	29.9
60°	24.9
62.5°	19.9
65°	14.9
67.5°	10.0
70°	10.0
72.5°	5.0
75°	5.0
77.5°	5.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)