

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202922

Luminaire Tested: **LE_6B15D010 EC6B10209040 6LBWGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202922
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209040 6LBWGPH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1058.8 lumens
Efficiency: N/A
Efficacy: 74.0 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.11
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202922

CATALOG NUMBER: LE_6B15D010 EC6B10209040 6LBWGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P202922

CATALOG NUMBER: LE_6B15D010 EC6B10209040 6LBWGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82			
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74			
4	93	84	77	72	91	82	76	72	80	75	71	78	74	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	81	71	64	59	80	70	63	59	68	62	58	67	62	58	65	61	57	56			
7	76	65	58	53	75	65	58	53	63	57	53	62	57	53	61	56	52	51			
8	72	61	54	49	70	60	53	49	59	53	49	58	52	48	57	52	48	47			
9	68	57	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43			
10	64	53	46	42	63	52	46	42	51	45	41	51	45	41	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202922

CATALOG NUMBER: LE_6B15D010 EC6B10209040 6LBWGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.8	6.4
10°-20°	190.1	18.0
20°-30°	272.0	25.7
30°-40°	271.1	25.6
40°-50°	172.7	16.3
50°-60°	63.7	6.0
60°-70°	15.9	1.5
70°-80°	4.8	0.5
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	529.9	50.0
0°-40°	801.0	75.7
0°-60°	1037.3	98.0
0°-90°	1058.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1058.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	720	
5°	716	68
15°	676	190
25°	594	272
35°	441	271
45°	222	173
55°	67	64
65°	15	16
75°	4	5
85°	0	1
90°	0	



TEST NUMBER: P202922

CATALOG NUMBER: LE_6B15D010 EC6B10209040 6LBWGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	719.6
2.5°	719.6
5°	716.0
7.5°	708.6
10°	699.6
12.5°	688.6
15°	675.9
17.5°	659.5
20°	641.2
22.5°	621.2
25°	593.9
27.5°	564.8
30°	526.5
32.5°	486.4
35°	440.9
37.5°	386.2
40°	329.8
42.5°	275.1
45°	222.2
47.5°	174.9
50°	131.1
52.5°	96.5
55°	67.4
57.5°	43.8
60°	29.1
62.5°	20.0
65°	14.6
67.5°	10.9
70°	9.1
72.5°	5.5
75°	3.6
77.5°	3.6
80°	1.9
82.5°	1.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)