

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204403

Luminaire Tested: **LE_6B40D010 EC6B30509040 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204403
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B40D010 EC6B30509040 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4329.7 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204403

CATALOG NUMBER: LE_6B40D010 EC6B30509040 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P204403

CATALOG NUMBER: LE_6B40D010 EC6B30509040 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			76
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66			66
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			57
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50			50
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45			45
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40			40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36			36
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32			32
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30			30

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204403

CATALOG NUMBER: LE_6B40D010 EC6B30509040 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.3	4.4
10°-20°	531.5	12.3
20°-30°	775.1	17.9
30°-40°	883.9	20.4
40°-50°	847.9	19.6
50°-60°	649.4	15.0
60°-70°	356.3	8.2
70°-80°	94.7	2.2
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1495.9	34.6
0°-40°	2379.9	55.0
0°-60°	3877.2	89.5
0°-90°	4329.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4329.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2011	
5°	1995	189
15°	1886	531
25°	1684	775
35°	1413	884
45°	1102	848
55°	728	649
65°	358	356
75°	83	95
85°	0	1
90°	0	



TEST NUMBER: P204403

CATALOG NUMBER: LE_6B40D010 EC6B30509040 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2010.9
2.5°	2005.8
5°	1995.4
7.5°	1979.8
10°	1959.0
12.5°	1922.6
15°	1886.2
17.5°	1844.6
20°	1797.9
22.5°	1740.8
25°	1683.5
27.5°	1626.4
30°	1553.6
32.5°	1486.1
35°	1413.4
37.5°	1340.6
40°	1267.9
42.5°	1189.9
45°	1101.6
47.5°	1013.2
50°	919.8
52.5°	821.0
55°	727.5
57.5°	633.9
60°	535.2
62.5°	441.6
65°	358.5
67.5°	275.4
70°	202.6
72.5°	135.1
75°	83.1
77.5°	36.4
80°	10.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)