

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202858

Luminaire Tested: **LE_6B40D010 EC6B30509040 6LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202858
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B40D010 EC6B30509040 6LBWWH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4142.8 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202858

CATALOG NUMBER: LE_6B40D010 EC6B30509040 6LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202858

CATALOG NUMBER: LE_6B40D010 EC6B30509040 6LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	71	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202858

CATALOG NUMBER: LE_6B40D010 EC6B30509040 6LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	247.3	6.0
10°-20°	735.5	17.8
20°-30°	1107.1	26.7
30°-40°	1132.0	27.3
40°-50°	687.5	16.6
50°-60°	193.6	4.7
60°-70°	29.4	0.7
70°-80°	9.6	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2090.0	50.4
0°-40°	3221.9	77.8
0°-60°	4103.1	99.0
0°-90°	4142.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4142.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2573	
5°	2584	247
15°	2604	735
25°	2417	1107
35°	1835	1132
45°	884	688
55°	192	194
65°	26	29
75°	10	10
85°	0	1
90°	0	



TEST NUMBER: P202858

CATALOG NUMBER: LE_6B40D010 EC6B30509040 6LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2573.1
2.5°	2573.1
5°	2583.5
7.5°	2599.1
10°	2599.1
12.5°	2609.5
15°	2604.4
17.5°	2593.9
20°	2557.5
22.5°	2505.5
25°	2417.1
27.5°	2318.4
30°	2183.2
32.5°	2022.1
35°	1835.0
37.5°	1627.0
40°	1387.9
42.5°	1138.4
45°	883.8
47.5°	655.0
50°	462.6
52.5°	311.9
55°	192.4
57.5°	114.4
60°	57.1
62.5°	36.4
65°	26.0
67.5°	20.8
70°	15.6
72.5°	10.4
75°	10.4
77.5°	5.2
80°	5.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)