

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204812

Luminaire Tested: **LE\_6B40D010 EC6B30508050 6LBCSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204812  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B40D010 EC6B30508050 6LBCSMW1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM  
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57  
W DL3-44.71 W DLE-39.33 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5937.9 lumens  
Efficiency: N/A  
Efficacy: 142.1 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204812

CATALOG NUMBER: LE\_6B40D010 EC6B30508050 6LBCSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204812

CATALOG NUMBER: LE\_6B40D010 EC6B30508050 6LBCSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204812

CATALOG NUMBER: LE\_6B40D010 EC6B30508050 6LBCSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	229.8	3.9
10°-20°	654.1	11.0
20°-30°	984.1	16.6
30°-40°	1166.2	19.6
40°-50°	1160.6	19.5
50°-60°	935.6	15.8
60°-70°	566.0	9.5
70°-80°	210.2	3.5
80°-90°	31.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1868.0	31.5
0°-40°	3034.2	51.1
0°-60°	5130.5	86.4
0°-90°	5937.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5937.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2425	
5°	2414	230
15°	2317	654
25°	2137	984
35°	1868	1166
45°	1511	1161
55°	1044	936
65°	568	566
75°	191	210
85°	25	31
90°	0	



TEST NUMBER: P204812

CATALOG NUMBER: LE\_6B40D010 EC6B30508050 6LBCSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2425.2
2.5°	2425.2
5°	2414.4
7.5°	2407.2
10°	2385.6
12.5°	2349.6
15°	2317.2
17.5°	2281.2
20°	2238.1
22.5°	2194.9
25°	2137.4
27.5°	2076.2
30°	2007.9
32.5°	1943.0
35°	1867.5
37.5°	1788.4
40°	1694.8
42.5°	1604.9
45°	1511.2
47.5°	1406.9
50°	1291.8
52.5°	1173.0
55°	1043.5
57.5°	928.4
60°	798.8
62.5°	683.6
65°	568.5
67.5°	460.6
70°	359.9
72.5°	269.9
75°	190.8
77.5°	122.4
80°	72.0
82.5°	43.1
85°	25.2
87.5°	10.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)