

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205023

Luminaire Tested: **LE\_6B40D010 EC6B30509050 6LBCS1MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205023  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B40D010 EC6B30509050 6LBCS1MMS  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM  
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57  
W DL3-44.71 W DLE-39.33 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4680.7 lumens  
Efficiency: N/A  
Efficacy: 112.0 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205023

CATALOG NUMBER: LE\_6B40D010 EC6B30509050 6LBCS1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P205023

CATALOG NUMBER: LE\_6B40D010 EC6B30509050 6LBCS1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	83	80	78	76			76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65			65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50			50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44			44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40			40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36			36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32			32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29			29

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205023

CATALOG NUMBER: LE\_6B40D010 EC6B30509050 6LBCS1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	202.6	4.3
10°-20°	568.4	12.1
20°-30°	830.2	17.7
30°-40°	949.6	20.3
40°-50°	912.6	19.5
50°-60°	704.6	15.1
60°-70°	393.3	8.4
70°-80°	114.5	2.4
80°-90°	4.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1601.2	34.2
0°-40°	2550.8	54.5
0°-60°	4168.0	89.0
0°-90°	4680.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4680.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2150	
5°	2131	203
15°	2016	568
25°	1804	830
35°	1520	950
45°	1190	913
55°	790	705
65°	394	393
75°	100	114
85°	3	5
90°	0	



TEST NUMBER: P205023

CATALOG NUMBER: LE\_6B40D010 EC6B30509050 6LBCS1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2149.5
2.5°	2149.5
5°	2131.4
7.5°	2122.2
10°	2092.0
12.5°	2055.6
15°	2016.4
17.5°	1977.0
20°	1919.4
22.5°	1874.0
25°	1804.4
27.5°	1734.8
30°	1665.1
32.5°	1595.5
35°	1519.8
37.5°	1444.1
40°	1356.4
42.5°	1277.6
45°	1189.8
47.5°	1089.9
50°	996.0
52.5°	893.1
55°	790.1
57.5°	684.2
60°	584.2
62.5°	484.4
65°	393.6
67.5°	308.8
70°	230.1
72.5°	160.5
75°	99.9
77.5°	51.5
80°	18.1
82.5°	6.0
85°	3.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)