

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204471

Luminaire Tested: **LE_6B20D010 EC6B10208027 6LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204471
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10208027 6LBSB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2231.3 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204471

CATALOG NUMBER: LE_6B20D010 EC6B10208027 6LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P204471

CATALOG NUMBER: LE_6B20D010 EC6B10208027 6LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76			76
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65			65
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50			50
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44			44
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39			39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35			35
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32			32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29			29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204471

CATALOG NUMBER: LE_6B20D010 EC6B10208027 6LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.9	4.2
10°-20°	263.6	11.8
20°-30°	392.1	17.6
30°-40°	456.3	20.4
40°-50°	444.7	19.9
50°-60°	342.1	15.3
60°-70°	189.1	8.5
70°-80°	50.1	2.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	748.6	33.5
0°-40°	1204.9	54.0
0°-60°	1991.7	89.3
0°-90°	2231.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2231.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	984	
5°	979	93
15°	933	264
25°	851	392
35°	732	456
45°	577	445
55°	382	342
65°	190	189
75°	42	50
85°	0	0
90°	0	



TEST NUMBER: P204471

CATALOG NUMBER: LE_6B20D010 EC6B10208027 6LBSB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	984.2
2.5°	984.2
5°	978.6
7.5°	970.1
10°	964.5
12.5°	947.5
15°	933.4
17.5°	919.2
20°	899.4
22.5°	879.6
25°	851.4
27.5°	823.0
30°	794.8
32.5°	763.6
35°	732.5
37.5°	693.0
40°	659.0
42.5°	622.2
45°	577.0
47.5°	534.6
50°	486.5
52.5°	435.6
55°	381.9
57.5°	330.9
60°	282.9
62.5°	234.8
65°	189.5
67.5°	147.1
70°	107.5
72.5°	73.5
75°	42.4
77.5°	19.8
80°	2.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)