

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204788

Luminaire Tested: **LE_6B20D010 EC6B10209027 6LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204788
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10209027 6LBCSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2297.7 lumens
Efficiency: N/A
Efficacy: 110.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204788

CATALOG NUMBER: LE_6B20D010 EC6B10209027 6LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204788

CATALOG NUMBER: LE_6B20D010 EC6B10209027 6LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204788

CATALOG NUMBER: LE_6B20D010 EC6B10209027 6LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.9	3.9
10°-20°	253.1	11.0
20°-30°	380.8	16.6
30°-40°	451.3	19.6
40°-50°	449.1	19.5
50°-60°	362.0	15.8
60°-70°	219.0	9.5
70°-80°	81.3	3.5
80°-90°	12.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	722.8	31.5
0°-40°	1174.1	51.1
0°-60°	1985.2	86.4
0°-90°	2297.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2297.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	938	
5°	934	89
15°	897	253
25°	827	381
35°	723	451
45°	585	449
55°	404	362
65°	220	219
75°	74	81
85°	10	12
90°	0	



TEST NUMBER: P204788

CATALOG NUMBER: LE_6B20D010 EC6B10209027 6LBCSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	938.5
2.5°	938.5
5°	934.2
7.5°	931.5
10°	923.1
12.5°	909.2
15°	896.6
17.5°	882.8
20°	866.0
22.5°	849.4
25°	827.0
27.5°	803.4
30°	776.9
32.5°	751.9
35°	722.6
37.5°	692.0
40°	655.8
42.5°	621.0
45°	584.8
47.5°	544.4
50°	499.9
52.5°	453.9
55°	403.8
57.5°	359.2
60°	309.1
62.5°	264.5
65°	220.0
67.5°	178.2
70°	139.2
72.5°	104.4
75°	73.8
77.5°	47.4
80°	27.9
82.5°	16.8
85°	9.8
87.5°	4.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)