

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204374

Luminaire Tested: **LE_6B20D010 EC6B10209027 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204374
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10209027 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1998.9 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204374

CATALOG NUMBER: LE_6B20D010 EC6B10209027 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P204374

CATALOG NUMBER: LE_6B20D010 EC6B10209027 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88			
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66			
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50			
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45			
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36			
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32			
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204374

CATALOG NUMBER: LE_6B20D010 EC6B10209027 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.4	4.4
10°-20°	245.4	12.3
20°-30°	357.8	17.9
30°-40°	408.1	20.4
40°-50°	391.5	19.6
50°-60°	299.8	15.0
60°-70°	164.5	8.2
70°-80°	43.8	2.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	690.6	34.5
0°-40°	1098.7	55.0
0°-60°	1790.0	89.5
0°-90°	1998.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1998.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	928	
5°	921	87
15°	871	245
25°	777	358
35°	652	408
45°	509	391
55°	336	300
65°	166	164
75°	38	44
85°	0	1
90°	0	



TEST NUMBER: P204374

CATALOG NUMBER: LE_6B20D010 EC6B10209027 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	928.4
2.5°	926.0
5°	921.1
7.5°	914.0
10°	904.4
12.5°	887.6
15°	870.8
17.5°	851.6
20°	830.0
22.5°	803.6
25°	777.2
27.5°	750.9
30°	717.2
32.5°	686.1
35°	652.5
37.5°	618.9
40°	585.4
42.5°	549.4
45°	508.6
47.5°	467.8
50°	424.6
52.5°	379.0
55°	335.9
57.5°	292.6
60°	247.1
62.5°	203.9
65°	165.5
67.5°	127.1
70°	93.5
72.5°	62.4
75°	38.4
77.5°	16.8
80°	4.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)