

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205037

Luminaire Tested: **LE_6B50D010R EC6B30509727 6LBCS1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205037
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30509727 6LBCS1MMS
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4908.3 lumens
Efficiency: N/A
Efficacy: 83.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205037

CATALOG NUMBER: LE_6B50D010R EC6B30509727 6LBSC1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P205037

CATALOG NUMBER: LE_6B50D010R EC6B30509727 6LBSC1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88	88	88	88
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76	76	76	76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65	65	65	65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57	57	57	57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50	50	50	50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44	44	44	44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40	40	40	40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36	36	36	36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32	32	32	32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29	29	29	29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205037

CATALOG NUMBER: LE_6B50D010R EC6B30509727 6LBCS1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	212.4	4.3
10°-20°	596.0	12.1
20°-30°	870.6	17.7
30°-40°	995.7	20.3
40°-50°	957.0	19.5
50°-60°	739.0	15.1
60°-70°	412.5	8.4
70°-80°	120.0	2.4
80°-90°	5.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1679.0	34.2
0°-40°	2674.7	54.5
0°-60°	4370.6	89.0
0°-90°	4908.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4908.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2254	
5°	2235	212
15°	2114	596
25°	1892	871
35°	1594	996
45°	1248	957
55°	829	739
65°	413	412
75°	105	120
85°	3	5
90°	0	



TEST NUMBER: P205037

CATALOG NUMBER: LE_6B50D010R EC6B30509727 6LBCS1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2254.0
2.5°	2254.0
5°	2235.0
7.5°	2225.4
10°	2193.8
12.5°	2155.6
15°	2114.4
17.5°	2073.0
20°	2012.8
22.5°	1965.1
25°	1892.1
27.5°	1819.1
30°	1746.0
32.5°	1673.0
35°	1593.6
37.5°	1514.2
40°	1422.2
42.5°	1339.8
45°	1247.6
47.5°	1142.9
50°	1044.5
52.5°	936.5
55°	828.6
57.5°	717.5
60°	612.8
62.5°	508.0
65°	412.8
67.5°	323.9
70°	241.2
72.5°	168.2
75°	104.8
77.5°	54.0
80°	19.0
82.5°	6.4
85°	3.1
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)