

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204271

Luminaire Tested: **LE_6B20D010 EC6B10209027 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204271
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10209027 6LBSWH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2190.6 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204271

CATALOG NUMBER: LE_6B20D010 EC6B10209027 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204271

CATALOG NUMBER: LE_6B20D010 EC6B10209027 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67			
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204271

CATALOG NUMBER: LE_6B20D010 EC6B10209027 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.5	5.5
10°-20°	311.9	14.2
20°-30°	408.0	18.6
30°-40°	432.0	19.7
40°-50°	402.9	18.4
50°-60°	305.2	13.9
60°-70°	165.2	7.5
70°-80°	44.4	2.0
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	840.4	38.4
0°-40°	1272.3	58.1
0°-60°	1980.4	90.4
0°-90°	2190.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2190.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1306	
5°	1287	120
15°	1115	312
25°	887	408
35°	690	432
45°	525	403
55°	343	305
65°	165	165
75°	38	44
85°	0	1
90°	0	



TEST NUMBER: P204271

CATALOG NUMBER: LE_6B20D010 EC6B10209027 6LBSWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1306.5
2.5°	1301.6
5°	1287.2
7.5°	1256.1
10°	1215.4
12.5°	1167.4
15°	1114.8
17.5°	1054.8
20°	1002.0
22.5°	942.1
25°	887.0
27.5°	831.9
30°	779.1
32.5°	733.5
35°	690.4
37.5°	647.2
40°	606.5
42.5°	565.8
45°	525.0
47.5°	479.4
50°	433.9
52.5°	388.4
55°	342.8
57.5°	294.9
60°	249.2
62.5°	206.1
65°	165.4
67.5°	127.0
70°	93.5
72.5°	64.8
75°	38.4
77.5°	16.8
80°	4.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)