

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203246

Luminaire Tested: **LE_6B20D010 EC6B10209727 6LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203246
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10209727 6LBMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1330.1 lumens
Efficiency: N/A
Efficacy: 63.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203246

CATALOG NUMBER: LE_6B20D010 EC6B10209727 6LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P203246

CATALOG NUMBER: LE_6B20D010 EC6B10209727 6LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53			
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49			
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203246

CATALOG NUMBER: LE_6B20D010 EC6B10209727 6LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.3	9.0
10°-20°	311.3	23.4
20°-30°	403.4	30.3
30°-40°	299.5	22.5
40°-50°	126.5	9.5
50°-60°	44.9	3.4
60°-70°	17.3	1.3
70°-80°	6.0	0.5
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	835.1	62.8
0°-40°	1134.6	85.3
0°-60°	1306.0	98.2
0°-90°	1330.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1330.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1316	
5°	1288	120
15°	1111	311
25°	895	403
35°	475	299
45°	156	126
55°	48	45
65°	17	17
75°	6	6
85°	0	1
90°	0	



TEST NUMBER: P203246

CATALOG NUMBER: LE_6B20D010 EC6B10209727 6LBMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1316.2
2.5°	1312.4
5°	1287.8
7.5°	1251.6
10°	1208.0
12.5°	1160.5
15°	1111.1
17.5°	1056.0
20°	1006.6
22.5°	955.4
25°	894.6
27.5°	811.0
30°	712.2
32.5°	596.4
35°	474.9
37.5°	372.2
40°	283.0
42.5°	210.9
45°	155.8
47.5°	114.0
50°	83.6
52.5°	62.6
55°	47.5
57.5°	36.1
60°	28.5
62.5°	20.9
65°	17.1
67.5°	13.2
70°	9.5
72.5°	7.6
75°	5.8
77.5°	3.8
80°	1.9
82.5°	1.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)