

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204212

Luminaire Tested: **LE\_6B50D010R EC6B30509727 6LBSH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204212  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B50D010R EC6B30509727 6LBSH1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4970.1 lumens  
Efficiency: N/A  
Efficacy: 84.5 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204212

CATALOG NUMBER: LE\_6B50D010R EC6B30509727 6LBSH1

### Luminous Intensity Polar Plot





TEST NUMBER: P204212

CATALOG NUMBER: LE\_6B50D010R EC6B30509727 6LBSH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF  | 20  |     |     |     |     |     |     |     |     | 20  |     |     |     |     |     |     |     |     | 20 |    |   |  |  |  |  |  |  | 20 |  |  |  |  |  |  |  |  |   |
| RC  | 80  |     |     |     |     |     |     |     |     | 50  |     |     |     |     |     |     |     |     | 30 |    |   |  |  |  |  |  |  | 10 |  |  |  |  |  |  |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 1   | 111 | 107 | 104 | 101 | 108 | 105 | 102 | 99  | 101 | 98  | 96  | 97  | 95  | 93  | 93  | 92  | 90  | 88  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 2   | 102 | 96  | 90  | 85  | 100 | 94  | 88  | 84  | 90  | 86  | 82  | 87  | 83  | 80  | 84  | 81  | 79  | 77  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 3   | 95  | 85  | 78  | 73  | 92  | 84  | 77  | 72  | 81  | 75  | 71  | 78  | 74  | 70  | 76  | 72  | 69  | 67  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 4   | 87  | 77  | 69  | 63  | 85  | 75  | 68  | 63  | 73  | 67  | 62  | 71  | 65  | 61  | 69  | 64  | 60  | 58  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 5   | 81  | 69  | 61  | 55  | 79  | 68  | 61  | 55  | 66  | 60  | 55  | 64  | 59  | 54  | 63  | 58  | 53  | 51  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 6   | 75  | 63  | 55  | 49  | 73  | 62  | 54  | 49  | 60  | 54  | 49  | 59  | 53  | 48  | 57  | 52  | 48  | 46  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 7   | 70  | 58  | 50  | 44  | 68  | 57  | 49  | 44  | 55  | 49  | 44  | 54  | 48  | 43  | 53  | 47  | 43  | 41  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 8   | 65  | 53  | 45  | 40  | 64  | 52  | 45  | 40  | 51  | 44  | 39  | 50  | 44  | 39  | 49  | 43  | 39  | 37  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 9   | 61  | 49  | 41  | 36  | 60  | 48  | 41  | 36  | 47  | 40  | 36  | 46  | 40  | 36  | 45  | 40  | 35  | 34  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 10  | 58  | 45  | 38  | 33  | 56  | 45  | 38  | 33  | 44  | 37  | 33  | 43  | 37  | 33  | 42  | 37  | 33  | 31  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204212

CATALOG NUMBER: LE\_6B50D010R EC6B30509727 6LBSH1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 243.5  | 4.9       |
| 10°-20°   | 661.8  | 13.3      |
| 20°-30°   | 919.0  | 18.5      |
| 30°-40°   | 1002.9 | 20.2      |
| 40°-50°   | 935.6  | 18.8      |
| 50°-60°   | 710.1  | 14.3      |
| 60°-70°   | 388.8  | 7.8       |
| 70°-80°   | 107.0  | 2.2       |
| 80°-90°   | 1.5    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1824.3 | 36.7      |
| 0°-40°    | 2827.2 | 56.9      |
| 0°-60°    | 4472.8 | 90.0      |
| 0°-90°    | 4970.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 4970.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2599 |      |
| 5°  | 2577 | 243  |
| 15° | 2358 | 662  |
| 25° | 1997 | 919  |
| 35° | 1603 | 1003 |
| 45° | 1215 | 936  |
| 55° | 794  | 710  |
| 65° | 388  | 389  |
| 75° | 93   | 107  |
| 85° | 0    | 1    |
| 90° | 0    |      |



TEST NUMBER: P204212

CATALOG NUMBER: LE\_6B50D010R EC6B30509727 6LBSH1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 2599.4 |
| 2.5°  | 2599.4 |
| 5°    | 2577.4 |
| 7.5°  | 2544.6 |
| 10°   | 2495.4 |
| 12.5° | 2429.6 |
| 15°   | 2358.5 |
| 17.5° | 2271.0 |
| 20°   | 2188.9 |
| 22.5° | 2090.4 |
| 25°   | 1997.4 |
| 27.5° | 1904.4 |
| 30°   | 1800.4 |
| 32.5° | 1701.9 |
| 35°   | 1603.4 |
| 37.5° | 1504.9 |
| 40°   | 1411.9 |
| 42.5° | 1313.4 |
| 45°   | 1214.9 |
| 47.5° | 1116.4 |
| 50°   | 1006.9 |
| 52.5° | 902.9  |
| 55°   | 793.5  |
| 57.5° | 689.5  |
| 60°   | 585.5  |
| 62.5° | 481.5  |
| 65°   | 388.5  |
| 67.5° | 301.0  |
| 70°   | 224.4  |
| 72.5° | 153.2  |
| 75°   | 93.0   |
| 77.5° | 43.8   |
| 80°   | 11.0   |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)