

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204379

Luminaire Tested: **LE_6B20D010 EC6B10209727 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204379
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10209727 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1738.6 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204379

CATALOG NUMBER: LE_6B20D010 EC6B10209727 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P204379

CATALOG NUMBER: LE_6B20D010 EC6B10209727 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76																			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66																			
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57																			
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50																			
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45																			
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40																			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36																			
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32																			
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204379

CATALOG NUMBER: LE_6B20D010 EC6B10209727 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.0	4.4
10°-20°	213.4	12.3
20°-30°	311.3	17.9
30°-40°	355.0	20.4
40°-50°	340.5	19.6
50°-60°	260.7	15.0
60°-70°	143.1	8.2
70°-80°	38.0	2.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	600.7	34.6
0°-40°	955.7	55.0
0°-60°	1556.9	89.5
0°-90°	1738.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1738.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	808	
5°	801	76
15°	757	213
25°	676	311
35°	568	355
45°	442	341
55°	292	261
65°	144	143
75°	33	38
85°	0	1
90°	0	



TEST NUMBER: P204379

CATALOG NUMBER: LE_6B20D010 EC6B10209727 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	807.5
2.5°	805.4
5°	801.2
7.5°	795.0
10°	786.6
12.5°	772.0
15°	757.4
17.5°	740.8
20°	722.0
22.5°	699.0
25°	676.0
27.5°	653.1
30°	623.9
32.5°	596.8
35°	567.5
37.5°	538.4
40°	509.1
42.5°	477.9
45°	442.4
47.5°	406.9
50°	369.4
52.5°	329.6
55°	292.1
57.5°	254.5
60°	214.9
62.5°	177.4
65°	144.0
67.5°	110.6
70°	81.4
72.5°	54.2
75°	33.4
77.5°	14.6
80°	4.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)